

Distributed by:



www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

1010 Series

Top Willing Co., Ltd.








D-SUB H.D. RIGHT ANGLE TYPE

Specifications:

Contact Resistance: 30mΩmax. at DC 100mA
Insulator Resistance: 1000MΩmin. at DC 500V
Current Rating: 3 AMP

Dielectric Withstanding

Voltage: AC 1000V For 1 minute
Operating Temperature: -55°C~+105°C
Contact: Brass or Phosphor Bronze
Housing: PBT & 30% Glass Fiber (UL 94V-0)



Dimension

Position	Dimension				
	A	B	C	D	E
15	16.3	0.25	2.29	24.99	30.8
26	24.7	0.51	2.29	33.32	39.1
44	38.4	0.51	2.29	47.04	53.0
62	54.8	0.58	2.41	63.50	69.3