



NOTES:

1. ALL DIMENSION IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
5. CONTACT RATING (NON-SWITCHING): 5A
6. OPERATING FORCE: 425 ± 100 CM/STANDARD
7. CONTACT MATERIAL: GOLD FLASH OVER SILVER PLATE
over COPPER ALLOY
8. OPERATING TEMP: -30° to 85°C
9. CIRCUIT SP: 6 POSITIONS, 30° INDEX.
10. DIELECTRIC STRENGTH: 1000V RMS min.@SEA LEVEL.
11. SHARDWARE SUPPLIED ON SWITCH – SEE BELOW
STOP RING, LOCKWASHER, & HEXNUT
12. ▲ DENOTES CRITICAL PARAMETER




CONTACT CONFIGURATION

Timing: Non Shorting (BBM)



RECOMMENDED P.C.B. LAYOUT



E-SWITCH®				
TITLE KC16A13.001NPF				
B	13172	21.00 WAS 38.00	6/2/03	AR
A	13164	RELEASED FOR PRODUCTION	5/28/03	AR
REV.	ECN NO.	DESCRIPTION	DATE	CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				
SCALE 1.5:1		DATE 5/28/03	DR AR	JWG G510711
				REV B