

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0982670322](#)  
**Status:** **Active**  
**Overview:** [Premo-Flex Cable Jumpers](#)  
**Description:** 1.00mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 152.00mm Cable Length, Tin (Sn) Plating, 16 Circuits

**Documents:**

|                                                                |                                                      |
|----------------------------------------------------------------|------------------------------------------------------|
| <a href="#">Drawing (PDF)</a>                                  | <a href="#">Datasheet (PDF)</a>                      |
| <a href="#">Packaging Specification PK-98267-001-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a> |

**General**

|                         |                                          |
|-------------------------|------------------------------------------|
| Product Family          | Cable                                    |
| Series                  | <a href="#">98267</a>                    |
| Comments                | Contacts on opposite sides, Type D       |
| Crimp Quality Equipment | Yes                                      |
| Overview                | <a href="#">Premo-Flex Cable Jumpers</a> |
| Product Name            | Premo-Flex FFC Jumper                    |
| UPC                     | 756054773239                             |

**Physical**

|                               |                 |
|-------------------------------|-----------------|
| Cable Length                  | 152.00mm        |
| Circuits (Loaded)             | 16              |
| Material - Plating Mating     | Tin             |
| Net Weight                    | 1.804/g         |
| Packaging Type                | Bag             |
| Pitch - Mating Interface      | 1.00mm          |
| Temperature Range - Operating | -40° to +105°C  |
| Wire Size AWG                 | N/A             |
| Wire/Cable Type               | Flat Flex Cable |

**Electrical**

|                               |        |
|-------------------------------|--------|
| Current - Maximum per Contact | 1.2A   |
| Voltage - Maximum             | 60V AC |

**Material Info**

**Reference - Drawing Numbers**

|                         |                  |
|-------------------------|------------------|
| Packaging Specification | PK-98267-001-001 |
| Sales Drawing           | SD-98267-001     |



Series image - Reference only

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

**China RoHS**

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

**Search Parts in this Series**

[98267 Series](#)

**Mates With**

Easy-On FFC/FPC Connector: <br>  
[522071633](#) , [522711679](#) , [526101633](#) ,  
[526101634](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION