

Knockdown Stacking Rack Cabinet *RCSC Series*



Ideal for AV or IT/Server applications, the RCSC Rack Cabinet features a stacking design that allows for up to three (3) cabinets* to be stacked atop each other. This Rack Cabinet is fully loaded and includes two (2) pairs of infinitely adjustable sliding EIA square-hole rails, punch-outs for cable entry and/or fan cooling and comes in a variety of sizes and depths.

The unique stacking feature enables your cabinet space to grow as your needs do
*Stack up-to three (3) 12U, two (2) 24U or one (1) of each cabinet atop each other using the required **RCSCBAY** baying kit. The 12U cabinet is a great starter cabinet for any small to medium sized business.

Features

- Constructed in 16-gauge steel.
- Includes two (2) pair of 19" EIA-310-D compliant square-hole mounting rails with rack unit markings.
- Four (4) embosses are included with support for optional levelling feet or casters.
- Grounding studs provided on body.
- The top and bottom of the RCSC includes two (2) laser knockouts (per side) for cable-entry or fans (includes gasket strip material).
- Includes a laser knockout rear gland plate for floor-level cable entry.
- Finished in rugged black powder paint.
- Ships unassembled in a flat pack container for easy handling and shipping protection.

Specifications

- Mounting rails are infinitely adjustable in depth and are fabricated of heavy duty 14-gauge steel, painted smooth black.
- Optional doors are available in solid, tinted acrylic with venting (see above-left) and high airflow vented.
 - Snap-in hinges can be mounted without having to bolt-on from inside the cabinet. In addition, the hinges can be mounted on the left or right.
- High airflow perforated doors for both front and rear of the cabinet are suggested for most server applications.
 - Perforated doors meet server manufacturer Free-Air-Ratio (FAR) requirements at 63%.
- For 36" depth cabinet side panels include cable entry knockouts.
- Tested to nearly double the suggested load rating of 1,500 lbs.
- RoHS Compliant.
- Manufactured in North America.

Gallery



Accessories

Universal Rack Shelf

**Rack Mount Locking Storage
Drawer**

Sliding Keyboard Shelf

Rack Unit Label

Horizontal Lacing Strip

Horizontal Ring Cable Manager

Mounting Hardware

Caster Set

Grill Fan Kits

**Adjustable Depth 4-Post Rack
Mount Shelf**

Four Post Mounting Sliding Shelf

Outlet Strips

Adjustable Depth Cable Manager

Horizontal Hinged Cable Manager

**Horizontal Steel Finger Cable
Manager**

Rack Panels

Grounding

Leveling Feet

Part No.	Overall Dimensions			Usable Mounting Dimensions			Rack Units	Shipping Weight
	Height	Width	Depth	Height	Width	Depth		
RCSC1902124BK1	25.00	24.00	24.50	21.00	19.00	22.99	12U	86 lb (39.1 kg)
RCSC1902131BK1	25.00	24.00	31.50	21.00	19.00	29.99	12U	100 lb (45.5 kg)
RCSC1902136BK1	25.00	24.00	36.00	21.00	19.00	29.99	12U	110 lb (50.0 kg)
RCSC1904224BK1	46.00	24.00	24.50	42.00	19.00	22.99	24U	120 lb (54.5 kg)
RCSC1904231BK1	46.00	24.00	31.50	42.00	19.00	29.99	24U	145 lb (65.9 kg)
RCSC1904236BK1	46.00	24.00	36.00	42.00	19.00	29.99	24U	135 lb (61.4 kg)

Optional Doors

Part No.	Part No.	Part No.	Use with Cabinet Panel Height	
Solid Door	Vented Door	Vented Window Door	Units	Rack Units
RCSC19021SDBK1	RCSC19021VDBK1	RCSC19021WDBK1	21.00	12U
RCSC19042SDBK1	RCSC19042VDBK1	RCSC19042WDBK1	42.00	24U

RCSC Baying Kit

Part No.	RCSCBAY
----------	---------

Data subject to change without notice