


General Specifications

Motor Protection: Auto Restart
Insulation Resistance: 10M Ohm or over with a DC500V
Megger
Dielectric Withstand Voltage: AC 700V 1st
Allowable Ambient Temperature Range:
-10 degree C ~ +70 degree C (Operating)
-40 degree C ~ +70 degree C (Storage)
(non-condensing environment)

4710KL product picture




4710KL panel cut out




Material

Casing: Plastic (Black) UL94V-0
Impeller: Plastic (Black) UL94V-0
Lead Wire: UL10368, AWG26, +Red, -Black

4710KL characteristic curve



4710KL product drawing



Detailed Specifications

Expected Life:	40 degree C 50,000 Hours (L10)
DC Fan:	Ball Bearing Fan
Nominal Voltage:	12
Operating Voltage Lower:	6
Operating Voltage Upper:	13.8
Current:	0.4
Input Power:	4.8
Speed:	2500
Max. Air Flow:	2.85
Max. Air Flow:	100.6
Max. Static Pressure:	40.9
Max. Static Pressure:	0.16
Noise:	38.5
Mass:	180
Fan Size:	119
Fan Width:	25