



Sample photo

Order symbol: P 161609
Product nbr: 7094280
Description: Enclosure
Remarks: Polyester

EAN: 6418074004390
El. number:
 Finland 3423664
 Denmark 8212005662
 Italy 7331040
 Sweden 2536221

Including: Base, cover with EPDM gasket and stainless steel cover screws.

Dimensions:		L	W	H	Rating:
mm:		160	160	91	Ingress Protection (EN 60529): IP 66/67
inch:		6.3	6.3	3.6	Impact Resistance (EN 50102): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		GRP			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7001			UV resistance: UL 508
Cover colour:		RAL 7001			Flammability Rating (UL 746 C 5): UL 94 5V
Cover screws material:		Stainless steel			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:		EPDM			NEMA Class: NEMA 1, 4, 4X, 12, 13
Temperatures:					Certificates:
Short term:		-50 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-60 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
PM 1616		Mounting plate			
ARM 0615		DIN-15 Mounting rail			
ARH 16		DIN-35 Mounting rail			
MRS 28541		Wall fastening lug set			
PH A & AH A/B		Hinge set			

