

## 2- und 3-polig, IP 66

### Fronteinbau Zentralbefestigung 22 mm



2-/3-polig






| Dauerstrom<br>( $I_N/I_{th}$ ) | Schaltleistung<br>AC-23B (A) | Frontschild | Artikelnummer     | ab Lager<br>lieferbar |
|--------------------------------|------------------------------|-------------|-------------------|-----------------------|
| <b>2-polig</b>                 | <b>230 V</b>                 |             |                   |                       |
| 20 A                           | 1,5 kW                       | 64 x 64     | KG10B T202/01 FT2 | •                     |
| <b>3-polig</b>                 | <b>3 x 400 V</b>             |             |                   |                       |
| 20 A                           | 5,5 kW                       | 64 x 64     | KG10B T203/01 FT2 | •                     |
| 25 A                           | 7,5 kW                       | 64 x 64     | KG20B T203/01 FT2 | •                     |
| 32 A                           | 11 kW                        | 64 x 64     | KG32B T203/01 FT2 | •                     |

| Dauerstrom<br>( $I_N/I_{th}$ ) | Schaltleistung<br>AC-23B (A) | Frontschild | Artikelnummer     | ab Lager<br>lieferbar |
|--------------------------------|------------------------------|-------------|-------------------|-----------------------|
| <b>2-polig</b>                 | <b>230 V</b>                 |             |                   |                       |
| 20 A                           | 1,5 kW                       | 64 x 64     | KG10B T102/01 FT2 |                       |
| <b>3-polig</b>                 | <b>3 x 400 V</b>             |             |                   |                       |
| 20 A                           | 5,5 kW                       | 64 x 64     | KG10B T103/01 FT2 | •                     |
| 25 A                           | 7,5 kW                       | 64 x 64     | KG20B T103/01 FT2 | •                     |
| 32 A                           | 11 kW                        | 64 x 64     | KG32B T103/01 FT2 | •                     |

2-polig



3-polig



| Frontschild | Bügel-Ø | Anzahl Schösser |
|-------------|---------|-----------------|
| 64 x 64     | 9       | 3               |

|               | A  | L    | G  | H  | R    | C max |
|---------------|----|------|----|----|------|-------|
| KG10B 2-polig | 64 | 57,4 | 48 | 50 | 40,1 | 6     |
| KG10B 3-polig | 64 | 66,9 | 48 | 50 | 40,1 | 6     |
| KG20B         | 64 | 68,3 | 42 | 54 | 40,1 | 6     |
| KG32B         | 64 | 68,3 | 42 | 54 | 40,1 | 6     |

