

Specification Sheet

Part Number: 157-00060



- Wide strap minimizes pinching of soft hoses and convoluted tubing.
- Clamping rails increase circumferential grip on varying bundle diameters.
- Locking stud mount pawls allow for easy hand insertion.
- Nut or weld nesting counterbore provides flush mounting at the base.

Stand Off Dual Clamp Tie, 26.10" Long, 0.31" Stud Dia, PA66HIRHSUV, Black, 250/pkg

Article Number	157-00060
Type	SDCTL
Color	Black (BK)
Quantity Per	pack
Product Description	Stand Off Dual Clamp Ties offer the same features as the standard dual clamp tie, with a standoff mount that secures the bundle away from the side of the frame rail. This protects the bundles from bolts and other protrusions.
Short Description	Stand Off Dual Clamp Tie, 26.10" Long, 0.31" Stud Dia, PA66HIRHSUV, Black, 250/pkg
Global Part Name	SDCTL-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)	100
Minimum Tensile Strength (Metric)	445
Length L (Imperial)	26.1
Length L (Metric)	663.0
Fixation Method	Weld Stud Fixing
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.5
Width W (Metric)	12.7
Bundle Diameter Min (Imperial)	0.37
Bundle Diameter Min (Metric)	9.5
Bundle Diameter Max (Imperial)	3.4
Bundle Diameter Max (Metric)	86.4
Height H (Imperial)	1.47
Height H (Metric)	37.30

Stud Diameter (Metric)	M8
Stud Diameter (Imperial)	5/16
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	250
Package Quantity (Metric)	250
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)