





LOC		DIST		REVISIONS				
ES	00	P	LTR	DESCRIPTION		DATE	DWN	APVD
		D9		ADD NEW DASH NUMBER -19		09AUG2012	ML	SZ
		d9						




ISOMETRIC VIEW



- 1 MATERIAL: THERMO PLASTIC, UL94 V-0.
- 2 COMPANY TRADEMARK, PART NUMBER, AND DATE CODE TO BE MARKED IN AREA SHOWN.
- 3 PANEL THICKNESS = .040±.005
- 4 CONNECTOR KEEP OUT ZONE.
- 5 POWER CONTACT REFERENCE:
PART NUMBER: 1600960 & 1600961
MATERIAL: COPPER ALLOY
FINISH (INTERFACE):.0000030 Au OVER .0000050 Ni
- 6 DASH NUMBERS INDICATED ARE NOT RELEASED FOR PRODUCTION.
- 7 VARIABLE DIMENSION SHOW ON THE TABLE.



REF:
POWER SECONDARY LOCK
PART NUMBER: 1600903-1



D9	3.465	7	2.825	3.175	.525	6ACP(8AWG)	2-292499-0
	1.840	.300	1.200	1.550	.475	3ACP(8AWG)	1-292499-9
	2.365	.375	1.725	2.075	.475	4P(8AWG)	1-292499-8
	2.040	.375	1.400	1.750	.500	3ACP(8AWG)	1-292499-6
D7	2.190	.300	1.550	1.900	.500	4ACP(10AWG)	1-292499-5
	1.940	.200	1.300	1.650	.425	5HDP(12AWG)	1-292499-4
	3.465	7	2.825	3.175	.525	6ACP(10AWG)	1-292499-3
	2.340	.200	1.700	2.050	.425	7HDP(12AWG)	1-292499-2
6	2.440	.300	1.800	2.150	.475	5ACP(8AWG)	1-292499-1
	2.440	.250	1.800	2.150	.450	6P(12AWG)	292499-8
	2.940	.250	2.300	2.650	.450	8P(12AWG)	292499-7
	1.940	.250	1.300	1.650	.450	4P(12AWG)	292499-4
	2.140	.300	1.500	1.850	.475	4ACP(12AWG)	292499-3
	2.440	.300	1.800	2.150	.475	5ACP(12AWG)	292499-2
	1.840	.300	1.200	1.550	.475	3ACP(12AWG)	292499-1
	DIM R REF	DIM S	DIM U	DIM L	DIM K	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. ZHAO 08AUG2006	TE Connectivity	
DIMENSIONS: INCHES		CHK S. ZHAO 08AUG2006		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S. ZHAO	NAME SLIDE TO LOCK PANEL MOUNT CABLE RECEPTACLE HOUSING, WITH GUIDES, MULTI-BEAM XL	
	0 PLC ±.01 1 PLC ±.01 2 PLC ±.01 3 PLC ±.005 4 PLC ±.002 ANGLES ±.002 FINISH ±.002	PRODUCT SPEC 108-2157 APPLICATION SPEC 114-13112		
MATERIAL : 7		WEIGHT -	SIZE A100779	RESTRICTED TO -
Customer Drawing		SCALE 1:1	SHEET 1	REV E

LOC		DIST		REVISIONS			
P	LYR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	

PART NUMBER	ROWS		POWER			
			P3	P2	P1	
292499-1	D					
	C					
	B					
	A					
3ACP						




PART NUMBER	ROWS		POWER					
			P5	P4	P3	P2	P1	
292499-2	D							
	C							
	B							
	A							
5ACP								

PART NUMBER	ROWS		POWER				
			P4	P3	P2	P1	
292499-3	D						
	C						
	B						
	A						
4ACP							

PART NUMBER	ROWS		POWER				
			P4	P3	P2	P1	
292499-4	D						
	C						
	B						
	A						
4P							

PART NUMBER	ROWS		POWER								
			P8	P7	P6	P5	P4	P3	P2	P1	
292499-7	D										
	C										
	B										
	A										
8P											

PART NUMBER	ROWS		POWER						
			P6	P5	P4	P3	P2	P1	
292499-8	D								
	C								
	B								
	A								
6P									



RM	STANDARD POWER CONTACT
RA	MFBL POWER CONTACT
CODE	DESCRIPTION
CONTACT TABLE	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. ZHAO	08AUG2006	 TE Connectivity	
DIMENSIONS: INCHES		CHK S. ZHAO	08AUG2006		
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		APVD S. YAO		SLIDE TO LOCK PANEL MOUNT CABLE RECEPTACLE HOUSING, WITH GUIDES, MULTI-BEAM XL	
		PRODUCT SPEC		SIZE	
		APPLICATION SPEC			
		WEIGHT			
MATERIAL		FINISH		DRAWING NO	
-		-		A100779C-292499	
Customer Drawing		SCALE		SHEET	
		1:1		2 of 3	
				REV E	

LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-

PART NUMBER	ROWS		POWER					
			P5	P4	P3	P2	P1	
I-292499-1	D C B A		RM	RA	RM	RA	RM	
5ACP								

PART NUMBER	ROWS		POWER			
			P3	P2	P1	
I-292499-6	D C B A		RM	RM	RM	
3ACP						

PART NUMBER	ROWS		POWER							
			P7	P6	P5	P4	P3	P2	P1	
I-292499-2	D C B A		RM		RM		RM		RM	
7HDP										

PART NUMBER	ROWS		POWER				
			P4	P3	P2	P1	
I-292499-8	D C B A		RA	RM	RM	RM	
4P							

D7

PART NUMBER	ROWS		POWER						
			P6	P5	P4	P3	P2	P1	
I-292499-3	D C B A		RM	RM	RM	RM	RM	RM	
6ACP									

.425
5PLC

PART NUMBER	ROWS		POWER			
			P3	P2	P1	
I-292499-9	D C B A		RM	RA	RM	
3ACP						

PART NUMBER	ROWS		POWER						
			P6	P5	P4	P3	P2	P1	
2-292499-0	D C B A		RM	RM	RM	RM	RM	RM	
6ACP									

.425
5PLC

PART NUMBER	ROWS		POWER					
			P5	P4	P3	P2	P1	
I-292499-4	D C B A		RM		RM		RM	
5HDP								

NO LOACING CONTACT

PART NUMBER	ROWS		POWER				
			P4	P3	P2	P1	
I-292499-5	D C B A		RA	RA	RM	RM	
4ACP							

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN S.ZHAO	08AUG2006	 TE Connectivity			
				CHK S.ZHAO	08AUG2006				
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:				NAME			
INCHES		0 PLC ±. -				PRODUCT SPEC			
		1 PLC ±.01				APPLICATION SPEC			
		2 PLC ±.005				SIZE		CAGE CODE	
		3 PLC ±.002				DRAWING NO		RESTRICTED TO	
		ANGLES ±.002				WEIGHT		Customer Drawing	
		FINISH #1*				SCALE		1:1	
MATERIAL						A100779		C-292499	
						SHEET		3 OF 3	
						REV		E	