




- >
- [Electrical](#)
- >
- [Network Solutions](#)
- >
- [Lighting Controls](#)
- >
- [Entertainment](#)
- >
- [Home Automation](#)
- >
- [Connected Home](#)
- >
- [Energy Management](#)
- >
- [Power Quality](#)



4729-C

Description
15 Amp, 125 Volt, NEMA L5-15R, 2P, 3W, Locking Connector,Industrial Grade,
Grounding, – Black-White

- Additional Product Information**
- [Dimensional Drawing](#)
 - [Wiring Diagram](#)


Product Features

Grounding: Grounding
Amperage: 15 Amp
Voltage: 125 Volt
NEMA: L5-15R
Pole: 2
Wire: 3
Cord Range: .240 – .700
Wire Gauge: 18-10 AWG
Blades/Contacts: Solid Brass
Body Material: Super Tough Nylon
Assembly Screws: Steel, Zinc Plated
Color: Black-White
Standards and Certifications: UL/CSA
Warranty: Lifetime Warranty

Color: Black-White



NEMA: L5-15R



Features and Benefits

- For fast assembly Black & White devices feature:
- i,— Backed-out, color-coded brass terminal screws
- i,— Deep slotted triple drive face module and cord clamp screws
- i,— Deep wire wells with transparent wiring chambers
- Single piece 0.035 inch thick contacts with NO rivets for longest life and continuous conductivity
- Nylon face module features Amperage, Voltage, and NEMA configuration molded into face for easy identification and replacement.
- Fluted nylon housing makes it easier to grip with gloves and in debris-laden environments
- Thick-walled, super tough nylon housing resists abuse and impact
- Single piece external cord clamp includes catalogue number and NEMA configuration for easy identification
- External cord clamp accepts wire mesh connection grips
- Connectors ship with standard white and black cord clamp. Color-coded cord clamps available to identify amperage or equipment. Choose from blue, green, yellow, red, and orange.