








0,95 MAX.

- 1 MATERIAL :
CONTACT; PHOSPHORBRONZE
REDUCED CROSS-TALK SHIELD; PHOSPHORBRONZE
HOUSING; GLASSFILLED POLYESTER (GRAY)
- 2 GENERAL CONTACT PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): 1,27µm NICKEL MIN. AND
ACTION PIN: 0,5µm TIN MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION
REFERENCE FOR EACH DASH NUMBER.
REDUCED CROSS-TALK SHIELD PLATING:
GOLD FLASH OVER 1,27 µm NICKEL MIN.
- 3 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 2.
- 4 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 1.
- 5 CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE
THE MARKING CAN APPEAR ON THE FRONT SIDE OR ON
THE BACK SIDE.
- 6 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
TOTAL 125 HOLES.
- 7 PLATED SPOT ONLY ON COMPONENT SIDE, FORMING ONE
CONTACT WITH PLATED THROUGH HOLES OF ROW C
8. FITS WITH INTEGRATED GROUND RETURN
UPPERSHIELD 5338107-2 AND LOWERSHIELD 5338108-2.
- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

SCALE 2,5:1



THIS DRAWING IS A CONTROLLED DOCUMENT.

THIS DRAWING IS A CONTROLLED DOCUMENT.			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm			
		0 - PLC	$\pm$ —
		1 - PLC	$\pm$ —
		2 - PLC	$\pm$ —
		3 - PLC	$\pm$ —
		4 - PLC	$\pm$ —
		± 0.2	
		ANGLES: $\pm$ —	
MATERIAL		FINISH	
—		—	

		 5100624-4
		5100624-1
FINISH	MATERIAL	PARTNUMBER

KIRAN		10AUG2004		 Tyco Electronics Tyco Electronics Corporation s-Hertogen Bosch, Netherlands,							
00IJ		23SEP2004									
00IJ		23SEP2004		NAME Z-PACK 2MM HM TYPE B 125 POS. FEMALE CONNECTOR WITH REDUCED CROSS-TALK SHIELD							
T SPEC											
08-19082											
ATION SPEC											
14-19029		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
-		A2		00779		C-5100624		-			
CUSTOMER DRAWING						SCALE 5:1		SHEET 1 OF 1		REV D	