

Search within category

GO

BUY NOW

DESIGN / INSTALL



IT9115-CUV8A

Panduit Belt-Ty™ in line locking ties are easy to use thanks to low-profile snag-free heads and a belt-like parallel entry lock. Plus, with weather-resistant Nylon 6.6 material, they're ideal for indoor and outdoor environments and harsh UV light. Light-heavy cross section, 15.3in, Tensile strength: 552, charcoal gray, 100pc.

Specs	Packaging Details	Tools	Documents	★ Add to Favorites	🛒 Add to BOM
Material	Nylon 6.6				
Application	General				
Color	Charcoal Gray				
Cross Section	Light-Heavy				
Length (In.)	15.30				
Length (mm)	389.0				
Locking Style	Locking				
Width (In.)	0.35				
Width (mm)	8.9				
Continuous Use Temperature Range	-76°F (-60°C) - 185°F (85°C)				
Plenum-Rated	No				
Tool	GTH-E				
Width In (mm)	0.35 (8.9)				
CE Compliant	Yes				
CSA Certified	No				
UL Listed (File #E56854)	No				
UL Recognized (File #E56854)	No				
Installation Temperature	-4°F (-20°C) - 32°F (0°C)				
Material Flammability Rating	UL 94V-2				
Max. Bundle Diameter (mm)	115.0				
Min. Loop Tensile Strength (N)	552				
Operating Temperature	-76°F (-60°C) - 185°F (85°C)				
Part Features	Parallel-entry tie that threads like a belt (180° entry). 50 pct lower head height than conventional 90° ties. Outside teeth protects cable jacket and wire insulation.				
Style	In-Line				
Type	In-Line/Low Profile Ties				
RoHS Compliancy Status	Compliant				
Min. Order Qty.	100				