

Product Description

Enables the use of cable glands with smaller connection threads than the existing threaded holes; With guide notch for O-ring; Assembling with wrench



Application range

- Equipment group II / Category 2G+1D
- Devices, machines and apparatus
- Mobile offshore and marine applications
- Chemical and petrochemical industry

Benefits

- Enables the use of cable glands with smaller connection threads than the existing threaded holes
- With guide notch for O-ring
- Assembling with wrench

Design

- Metric connection thread acc. to EN 50262

Technical Data

Material

Body: Nickel plated brass O-Ring: NBR

Range of temperature

-30°C up to +90°C

Article List

Part number	Thread/ male M1	Thread/ female M2	Overall height mm	Thread length D mm	Outer Ø mm	Pieces / PU
SKINDICHT® MR-M ATEX						
52104570	16 x 1,5	12 x 1,5	10.5	5	19	50
52104571	20 x 1,5	16 x 1,5	13	6	24,5	50
52104572	25 x 1,5	20 x 1,5	15	7	30,1	25
52104573	32 x 1,5	25 x 1,5	16.5	8	37,2	25
52104574	40 x 1,5	32 x 1,5	16.5	8	45,6	10
52104575	50 x 1,5	40 x 1,5	19.5	10	55,3	5
52104576	63 x 1,5	50 x 1,5	18.5	8.5	71,3	5

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.