





REV.	DATE	DESCRIPTION
NC	05/15/02	INITIAL RELEASE



RECOMMENDED CABLE
STRIPPING DIMENSIONS



CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .324"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .100"

8				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS	APPROVALS	DATE	Amphenol - Connex CONNECTOR CORPORATION			
7										
6										
5										
4	FERRULE	BRASS	NICKEL	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .XXX = ± 0.005" .XX = ± 0.010" .X = ± 0.020"	ISSUED		TITLE BNC CRIMP PLUG (FOR TIMES LMR-300)			
3	CONTACT PIN	BER. COPPER	GOLD							
2	INSULATOR	TEFLON	NATURAL							
1	BODY	BRASS	NICKEL							
	DESCRIPTION	MATERIAL	FINISH	DO NOT SCALE DRAWING			SIZE	FSCM NO.	DWG. NO.	REV.
							A	99001	112700.DWG	NC
							SCALE	PART NO.	SHEET	
							NA	112700	1 OF 1	