

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 6814: ADDED NOTES 3 & 4, ADDED LABEL EXAMPLE, ROHS STAMP	4/25/13	D.FRISIELLO
F	ECN 7198: ADDED TOLERANCE TO LENGTHS, REVISED ROHS, FORMAT	12/16/13	D.FRISIELLO
G	ECN 7796: CHANGE "SJT 18AWG x 3" TO "SJT 17AWG x 3"	2/9/15	D.FRISIELLO






TABLE	
P/N	LENGTH
PCM1040	3'-3" ± .8"
PCM1042	6'-7" ± 2.0"
PCM1044	9'-10" ± 2.4"


BAG LABEL EXAMPLE

PN: PCM104x

NOTES:

1. APPROVALS: UL/CSA, VDE, DEMKO, SEMKO, NEMKO
2. COLOR CODE: BLUE, BROWN, GREEN/YELLOW
3. CORD TO BE PLACED IN A CLEAR BAG WITH WHITE LABEL: "PN: PCM104x"
4. CENTER THE LABEL ON THE CLEAR BAG.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [13]	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY M.LAHEY	11/03/04			
	CHECKED BY C.MCCORMICK	11/03/04	CATEGORY	POWER PRODUCTS	
	APPROVED BY R.CARRICK	11/03/04	PRODUCT DESCRIPTION		
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		POWER CORD C14 TO C13			
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. PCM1040	REV. G
		SCALE: NONE	CAD FILE: PCM1040.SLDDRW	SHEET 1 OF 1	