


IEEE 1394 Firewire, 6 Pin Receptacle Right Angle (SMT) 154-FWR41

KOBICONN

IEEE 1394 Firewire, 6 Pin Receptacle Right Angle (SMT)



Dimensions: mm (In.)

Specifications	
Withstanding Voltage:	DC 500 ±50V
Insulation Resistance:	100 Megaohms min.
Contact Resistance:	30 Milliohms max.
Housing:	High Temperature Thermoplastics
Shell:	Copper Alloy
Contacts:	Copper Alloy

Date Last Revised: 6/25/12

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300188

154-FWR41

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-FWR41](#)