



WELCOME TO  
ACCURATE SCREW MACHINE  
A Division of MW Industries

[Login / Register](#)
[ENTER](#)

[HOME](#)
[ABOUT ASM](#)
[QUALITY](#)
[TECH TIPS](#)
[CREDIT](#)
[CHAT](#)
[E-SERVICES](#)
[RFQ](#)
[CALL US TOLL-FREE: 1.877.285.2181](#)

[CONTACT ASM](#)


### Product Search

By Part No.:

By

Keyword:

[ENTER](#)


### View Products



- [Bushings](#)
- [Captive Screws & Assemblies](#)
- [Handles / Ferrules](#)
- [Locking Fasteners](#)
- [Nuts](#)
- [Panel Screw Retainers](#)
- [Screws - Standard, Set, Stud](#)
- [Spacers](#)
- [Springs](#)
- [Standoffs / Adapters](#)
- [Thumb Screws](#)
- [Tools](#)
- [Washers](#)
- [Custom Parts](#)
- [Optional Product Features](#)



## FLAT HEAD PIN SOCKET CAPTIVE SECURITY SCREWS



D=.480-.531 H=.016-.161 J=5/32 K=1/4 B=0.175 L=.500-2.000

18-8 Stainless Steel only. Standard fastener products having a 3A thread, once plated may not enter 2A GO and NO-GO gages.

**Complete ASM Part No.: 115094 .5 SS 1**

[Metric Size Info](#)
[Help](#)
[Get .DXF File](#)
[Back to Product Index](#)

Printed catalog page(s): 146

Tolerance(s): K:  $\pm 0.010$  B:  $\pm 0.005$  L:  $\pm 1/32$

**Step 3 of 3: Click here to add part & download CAD Drawings or**  
**Edit values below and click** [Up-date](#) **again**

Length	Material	Finish
Please enter value in the box below:  .5	Stainless Steel, 18-8	No finish
		Anodized (Dk. Gray) Anodized (Clear) Anodized (Blue) Anodized (Red) Anodized (YellowGreen) Anodized (Dichromate) Anodized (Dyed Gold) Anodized (Black) Cadmium Clear Plate