


# Mini-Din Plugs

171-2603, 171-2604, 171-2605,  
171-2606, 171-2608

**KOBI**CONN

Mini-Din Plugs

171-2603, 171-2604, 171-2605, 171-2606, 171-2608



## SPECIFICATIONS

|                               |                       |
|-------------------------------|-----------------------|
| <b>Voltage Rating:</b>        | 100VAC 1A max.        |
| <b>Insulation Resistance:</b> | 50M $\Omega$ @ 500VDC |
| <b>Dielectric:</b>            | 500VAC for 1 minute   |
| <b>Contact Resistance:</b>    | 30m $\Omega$ max.     |
| <b>Acceptable Wire Size:</b>  | 24AWG - 28AWG         |
| <b>Boot:</b>                  | PVC                   |
| <b>Housing:</b>               | ABS                   |
| <b>Shell:</b>                 | nickel plated brass   |
| <b>Insulator:</b>             | polycarbonate         |
| <b>Pins:</b>                  | silver plated brass   |
| <b>Solder Temperature:</b>    | 200°C within 1 sec.   |
| <b>Assembly:</b>              | yes                   |

Dimensions: mm (in.)

## ASSEMBLY SPECIFICATIONS

|   |                   |                       |
|---|-------------------|-----------------------|
| 1 | <b>Cover:</b>     | PVC black             |
| 2 | <b>Con:</b>       | A.B.S.                |
| 3 | <b>Shell:</b>     | bronze, nickel plated |
| 4 | <b>Insulator:</b> | PC (or nylon)         |
| 5 | <b>Pins:</b>      | bronze                |

Date Last Revised: 02/19/21

Available from Mouser Electronics  
1-800-346-6873  
www.mouser.com

KC-300256

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.