


6



SPECIFICS PLATING AREA FOR PART NUMBERS :

- P/N 76745-1CH-10LF
- P/N 76745-1CH-18LF
- P/N 76745-579R24LF
- P/N 76745-579R30LF
- P/N 76745-1CU-20LF
- P/N 76745-1DF-26LF

AREA "A" & "B" : GOLD/GXT PLATING AREA



mat'l. code				surface ISO 1302 ☒ ISO 406 ISO 1101			projection 		product family BSTIK			
ltr	ecn no	dr	date	tolerances unless otherwise specified					title HEADER STR,DR DOUBLE BODY			
A	F06-110	LMU	06.01.26	angles	linear		mm					
B	F06-0196	LMU	06.06.20				scale					
C	F07-0266	J.CO	07.10.15									
D	F12-0023	LMU	12.06.06	dr	L.MULIN	06.01.31			dwg no 76745			
E	F12-0090	JFA	12.12.07	enr	J.COMPAGNON	06.01.31			sheet 3 of 4 size A3			
F	B-16665	LMU	14..01.06	chr								
				appd	JMC	06.01.31			type CUSTOMER Drawing			
sheet index	revision sheet											



SPECIFIC PRODUCT NUMBER

76745-3DCA04LF

— RoHS COMPLIANT
 — TOTAL NB OF POS
 — PACKAGING TYPE, SEE NOTE 1
 — PIN STYLE
 — PLATING
 3 = 2µm MATTE TIN
 OVER 1.27µm Ni MIN

NOTES :

1. PACKAGING : A = TAPE & REEL PACKAGING
WITH PICK UP CAP INSTALLED
SEE TA 840
2. PRODUCT COMPATIBLE WITH REFLOW PROCESS.
255°C PEAK TEMPERATURE 10-40 SECONDES IN
A CONVECTION, INFRA-RED OR VAPOR PHASE



mat'l. code				surface	tolerance	projection	product family			
lfr	ecn no	dr	date	ISO 1302	ISO 406	ISO 1101	BSTIK			
A	B-16665	LMU	14.01.06	tolerances unless otherwise specified			title			
				angles	linear	mm	HEADER STR,DR			
						scale	DOUBLE BODY			
				dr	L.MULIN	13.02.18	dwg no	sheet 4 of 4	size	
				engr	J.COMPAGNON	13.02.18	76745		A3	
				chr						
				appd	JMC	13.02.18	type		CUSTOMER Drawing	
sheet	revision									
index	sheet									