



EDL Lighting Ltd



Version: Haloflex-3x1W-IP20-12/24V-AC/DC Spotlight RS Order Code: 794-3493

The Haloflex is designed for maximum positioning flexibility in the head movement. A on/off switch is fitted on the head for ease of use. The flexible gooseneck is 700mm long. This unit is Ideal for a variety of applications including machine tools, wood working, general bench illumination and many commercial applications

A range of accessories are available to increase the advantages of this luminaire

Primary voltage:	12/24vAC/DC
Secondary voltage:	N/a
Lamp type:	LED
Wattage:	3x1 watt
Switch fitted Yes/No:	Yes
Switch location:	On Head
IP Rating	IP21
Base Type:	Screw down
Fixing:	Can be horizontal or vertically mounted
No of arms:	1
Length of arms	700mm flexible
Arm Material:	Covered flexible steel
Shade size and material:	70mm diameter moulded plastic
Shield fitted:	No (available as accessory)
Shield material	Clear acrylic or polycarbonate
Visor fitted:	No
Articulation movement:	Flexible
Joint type:	Flexible
Trailing cable:	Yes
Plug fitted	No
Manufacturing Standard:	BS EN 60598
RHOS compliant	Yes
WEE Compliant	Yes
Finish & Colour:	Black

EDL Lighting Limited, Redbrook lane, Brereton, Rugeley, Staffs WS15 1QU

Telephone: +44(0)1889 582112

Fax: +44(0)1889 584012

Email: sales@edl-lighting.co.uk Website www.edl-lighting.co.uk



EDL Lighting Ltd

Features

Choice of input voltage 12 or 24v

700mm flexible arm length

3x1w LED lamp unit fitted

Screw down base

Switch on head

Protective lens available (optional extra)

Option accessories include wall bracket, magnet, lens cover and clamp

Clamp



RS Code 794-3500



Clamp Fitted
to Base

Magnet



RS Code 794-3490



Magnet Fitted
to Base

Wall Bracket



RS Code 794-3503



Wall Bracket
Fitted to
Base

EDL Lighting Limited, Redbrook lane, Brereton, Rugeley, Staffs WS15 1QU

Telephone: +44(0)1889 582112

Fax: +44(0)1889 584012

Email: sales@edl-lighting.co.uk Website www.edl-lighting.co.uk