

Mini IR Thermometer



Mini size design

For the ultimate in convenience and portability

Features:

- Temperature range from -34 to 446°F (-33 to 230°C)
- Economical mini size design for convenience
- Automatic Data Hold when measure button is released
- Max Hold or Min Hold
- Lock feature for continuous scanning
- Fixed emissivity covers 90% of surface applications
- Auto power off
- Complete with CR2032 3V battery

Applications:

- Measure hot spots in electrical panels and equipment
- In Process temperature measurements
- Measure surface temperature of objects that are unsafe to contact
- Measure surface temperature of objects that hard to reach



Convenient Mini size

Specifications	
Range:	-34 to 446°F (-33 to 230°C)
Basic Accuracy:	±(2.0%rdg) or ±4°F/±2°C
Max. Resolution:	0.1°F/°C
Emissivity:	0.95 fixed
Field of View (Distance to Target):	1:1
Dimensions:	3 x 1.6 x 0.7" (75 x 40 x 18mm)
Weight:	1.5oz (43g)

Ordering Information:

IR100Mirco IR Thermometer

