

Savigny Oddie Limited

...one stop shop for all your hardware requirements

Contents

Hinges

Piano Hinges	Page 3
Lift Off Hinges	Page 7
Cabinet Hinges - Large	Page 14
Cabinet Hinges - Medium	Page 26
Cabinet Hinges - Small	Page 41
Made to Order Hinges	Page 49
Plastic Hinges	Page 54

Savigny Oddie Limited

...one stop shop for all your hardware requirements

Savigny Oddie Limited

...one stop shop for all your hardware requirements


Piano - Continuous Hinges

On request and according to quantity we can:

- supply hinges cut to length
- supply continuous hinges with holes
- crank or curve leaves
- replace the steel pin in the steel hinge with a non ferrous or stainless pin.

Available in:

- Steel
- Aluminium
- Brass
- Stainless Steel



Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk

Savigny Oddie Limited

...one stop shop for all your hardware requirements

Steel Without Holes - supplied in 2mtr lengths

Dimensions (mm)				Nominal Weight Kg/M	Part Number
A	B	C	D		
10	0.6	1.5	16	0.102	380331
10	0.6	1.5	20	0.125	380332
13	1.5	3	30	0.490	380333
13	1.5	3	40	0.610	380334
13	1.5	3	50	0.730	380335
13	1.5	3	65	0.910	380336
13	1.5	3	80	1.090	380340
13	1.5	3	120	1.570	380341
13	1.5	3	200	2.530	380337
13	1.5	3	240	3.010	380338
15	0.7	2.4	20	0.180	380339
15	0.7	2.4	25	0.206	380343
15	0.7	2.4	30	0.240	380344
16	0.8	3	35	0.318	380346
16	0.8	3	40	0.360	380347
16	1	2.7	20	0.265	380348
16	1	2.7	25	0.300	380349
16	1	2.7	30	0.335	380350
16	1	2.7	40	0.405	380351
16	1	2.7	50	0.490	380352
20	1.2	3	40	0.530	380354
20	1.2	3	50	0.610	380355
20	1.2	3	60	0.690	380356
25	1.5	5	30	0.670	380357
25	1.5	5	40	0.800	380453
25	1.5	5	50	0.900	380358
30	1.5	4	40	0.720	380361
30	1.5	4	50	0.850	380362
30	1.5	4	60	0.970	380363
30	2	6	40	1.120	380365
30	2	6	50	1.270	380366
30	2	6	60	1.470	380367
30	2	6	70	1.570	380369
30	2	6	80	1.700	380370
40	2	8	80	1.950	380371
40	2.5	8	50	1.770	380372
40	2.5	8	60	1.900	380373
40	2.5	8	70	2.170	380374
40	2.5	8	80	2.350	380375
50	3	10	75	2.970	380376

Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk

Savigny Oddie Limited

...one stop shop for all your hardware requirements

Aluminium Alloy Without Holes - supplied in 2mtr lengths

Dimensions (mm)				Nominal Weight Kg/M	Part Number	Notes
A	B	C	D			
15	0.7	2.4	20	0.085	380377	supplied with steel pin
15	0.7	2.4	25	0.095	380456	supplied with steel pin
15	0.7	2.4	30	0.105	380378	supplied with steel pin
16	1	2.7	35	0.105	380408	supplied with steel pin
16	1	2.7	40	0.175	380409	supplied with steel pin
16	1	2.7	50	0.200	380410	supplied with steel pin
20	1.2	3	40	0.175	380411	
20	1.2	3	50	0.208	380412	
20	1.2	3	60	0.242	380413	
25	1.5	3	70	0.375	380414	supplied with steel pin
30	1.5	4	40	0.260	380415	
30	1.5	4	50	0.300	380416	
30	1.5	4	60	0.350	380417	
30	2	6	40	0.400	380418	
30	2	6	50	0.455	380419	
30	2	6	60	0.510	380420	

Brass Without Holes - supplied in 2mtr lengths except where specified

Dimensions (mm)				Nominal Weight Kg/M	Part Number	Notes
A	B	C	D			
10	0.5	1.6	14	0.105	380383	supplied with steel pin
10	0.5	1.6	18	0.130	380386	supplied with steel pin
15	0.7	2.4	25	0.230	380389	supplied with steel pin
15	0.7	2.4	30	0.255	380391	supplied with steel pin
16	0.8	3	35	0.335	380436	
16	0.8	3	40	0.390	380437	
25	1.5	3	40	0.570	380438	supplied in lengths of 1.34m
30	2	6	40	1.270	380439	supplied in lengths of 1.34m
30	2	6	50	1.415	380440	supplied in lengths of 1.34m
30	2	6	60	1.565	380441	supplied in lengths of 1.34m

Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk

Savigny Oddie Limited

...one stop shop for all your hardware requirements

Stainless Steel Without Holes - supplied in 2mtr lengths

Dimensions				Nominal Weight Kg/M	Part Number
A	B	C	D		
15	0.6	2.5	20	0.140	380421
15	0.6	2.5	25	0.165	380394
15	0.6	2.5	30	0.190	380395
20	1	3	20	0.275	380396
20	1	3	25	0.325	380397
20	1	3	30	0.375	380398
20	1.2	3	40	0.520	380399
20	1.2	3	50	0.620	380400
20	1.2	3	60	0.700	380401
30	1.5	4	40	0.720	380402
30	1.5	4	50	0.850	380403
30	1.5	4	60	0.980	380404
30	2	6	40	1.120	380405
30	2	6	50	1.270	380406
30	2	6	60	1.470	380407
30	2	6	70	1.570	380380
30	2	6	80	1.700	380381

Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk





Savigny Oddie Limited

...one stop shop for all your hardware requirements

Lift Off Hinges


Contents

Lift Off Hinges

			
652 Page 8	653 Page 9	450 Page 10	650 Page 11
			
651 Page 12	421 Page 13		

Savigny Oddie Limited

...one stop shop for all your hardware requirements




Lift Off Hinges - Type 652

Lift off hinge for screw fixing.
Supplied with fixing screws, fan washers and collars.

Type 652

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
Steel	zinc & clear passivate	screws supplied	10.00	530019
Stainless Steel	natural	screws supplied	10.00	530020




Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk

Savigny Oddie Limited

...one stop shop for all your hardware requirements




Lift Off Hinges - Type 653

Lift off hinge for screw fixing.
Supplied with fixing screws, fan washers and collars.

Type 653

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
steel	zinc & clear passivate	screws supplied	10.00	530021




Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk


Savigny Oddie Limited

...one stop shop for all your hardware requirements



Lift Off Hinges - Type 450

Type 450 has a steel pin of 6mm diameter and is fitted with a brass washer.



Type 450 - Vertical Type

Dimensions (mm)			Material	Finish	Nominal Weight Kg/100	Part Number
A	B	C				
60	50	1.5	Steel	None	4.300	380284
70	50	1.5	Steel	None	4.800	380285
80	50	1.5	Steel	None	5.400	380286
90	50	1.5	Steel	None	5.900	380287
100	50	1.5	Steel	None	6.500	380288


Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk


Savigny Oddie Limited

...one stop shop for all your hardware requirements



Lift Off Hinges - Type 650

Roller lift off hinge for welding.
Manufactured from precision drawn steel with brass bearing washer.
Supplied with a steel pin fixed to one roller.



Type 650

Dimensions				Material	Finish	Nominal Weight Kg/100	Part Number
A	B	C	E				
60	10.0	6.0	12.0	Steel	natural	3.7	530003
80	13.0	8.0	15.5	Steel	natural	8.1	530005
100	16.0	10.0	20.0	Steel	natural	12.2	560007
120	16.0	11.0	20.0	Steel	natural	19.6	530008
150	20.0	13.0	25.5	Steel	natural	38.6	530010
180	20.0	14.0	25.5	Steel	natural	47.0	530011


Tel: 01384 271912

Fax: 01384 402443

www.savigny-oddie.co.uk

Savigny Oddie Limited

...one stop shop for all your hardware requirements




Lift Off Hinges - Type 651

Roller lift off hinge for welding.

Manufactured from precision drawn stainless steel with stainless steel bearing washer.

Supplied with a stainless steel pin fixed to one roller.

Dimensions				Material	Finish	Nominal Weight Kg/100	Part Number
A	B	C	E				
60	10.0	6.0	12.0	stainless steel	natural	3.7	530013
80	13.0	8.0	15.5	stainless steel	natural	8.1	530014
100	16.0	10.0	20.0	stainless steel	natural	12.2	530015
120	16.0	11.0	20.0	stainless steel	natural	19.6	530016
150	20.0	13.0	25.0	stainless steel	natural	38.6	530017
180	20.0	14.0	25.0	stainless	natural	47.0	530018




Tel: 01384 481598

Fax: 01384 482383


www.savigny-oddie.co.uk

Savigny Oddie Limited

...one stop shop for all your hardware requirements



Lift Off Hinges - Type 421



Type 421 - Horizontal Type

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
Steel	Zinc & Passivate	Holes	3.600	380127
18/8 Stainless Steel	None	Holes	3.600	380328

Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk










Savigny Oddie Limited

...one stop shop for all your hardware requirements

Cabinet Hinges - Large


Contents

Cabinet Hinges - Large

			
417 Page 15	1422 Page 16	422 Page 17	413 Page 18
			
470 Page 19	409 Page 20	473 Page 21	400 Page 22
			
430 Page 23	431 Page 24	433 Page 25	

Savigny Oddie Limited

...one stop shop for all your hardware requirements




Cabinet Hinges - Large Type 417

The movement of the hinge is limited to slightly over 180°
 The pin is made from 18/8 stainless steel in all cases except for unplated steel item.
 The pin is riveted at both ends.

Type 417

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
Steel	None	Holes	7.000	380207
Steel	Zinc & Passivate	Holes	7.000	380208
18/8 Stainless Steel	None	Holes	7.000	380206




Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk

Savigny Oddie Limited


...one stop shop for all your hardware requirements



Cabinet Hinges - Large Type 1422

Two torsion springs hold the hinge in the open position.

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
steel	zinc & passivate	holes	4.80	530045
stainless steel	natural	holes	4.90	530046




Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk


Savigny Oddie Limited

...one stop shop for all your hardware requirements



Cabinet Hinges - Large Type 422

Suitable for welding or screw fixing.



Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
steel	natural	holes	5.00	530028
steel	natural	no holes	5.20	530029
steel	zinc & passivate plated	holes	5.00	530030
stainless steel	natural	holes	5.00	530031
stainless steel	natural	no holes	5.20	530032


Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk

Savigny Oddie Limited


...one stop shop for all your hardware requirements



Cabinet Hinges - Large Type 413

Supplied with two slots and two M6 tapped holes.

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
steel	natural	slots & tapped holes	9.38	530033




Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk


Savigny Oddie Limited

...one stop shop for all your hardware requirements



Cabinet Hinges - Large Type 470

Double leaf design.
Suitable for welding or screw



Type 470

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
steel	natural	holes	13.00	530038
steel	natural	no holes	13.5	530039
steel	zinc & passivate	holes	13.00	530040
stainless steel	natural	holes	13.00	530041
stainless steel	natural	no holes	13.50	530042


Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk


Savigny Oddie Limited

...one stop shop for all your hardware requirements



Cabinet Hinges - Large Type 409 (Double Leaf)

The pin for type 409 is made from brass in all cases and is riveted at both ends.



Type 409

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
Steel	None	Holes	32.500	380258
18/8 Stainless Steel	None	Holes	32.500	380259


Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk


Savigny Oddie Limited

...one stop shop for all your hardware requirements




Cabinet Hinges - Large Type 473

Two torsion springs hold the hinge in the closed position.



Type 473

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
steel	zinc & passivate	holes	2.20	530043
stainless steel	natural	holes	2.40	530044




Material	Finish	Fixing	Nominal Weight kg/100	Part Number
steel	zinc plate	holes	11.00	530035



Savigny Oddie Limited


...one stop shop for all your hardware requirements



Cabinet Hinges - Large Type 430

Type 430 - as 431 but flat

Material	Fixing	Nominal Weight Kg/100	Part Number
steel, zinc and passivate plated	CSK Holes	11.595	380452




Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk

Savigny Oddie Limited


...one stop shop for all your hardware requirements



Cabinet Hinges - Large Type 431

Type 431

Material	Fixing	Nominal Weight Kg/100	Part Number
steel, zinc and passivate plated	CSK Holes	14.850	380297




Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk


Savigny Oddie Limited

...one stop shop for all your hardware requirements



Cabinet Hinges - Large type 433

With countersunk fixing holes.



Type 433

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
steel	zinc & passivate plated	countersunk holes	14.15	530034











Savigny Oddie Limited

...one stop shop for all your hardware requirements

Cabinet Hinges - Medium


Contents

Cabinet Hinges - Medium

			
605 Page 27	406 Page 29	405 Page 31	403 Page 33
			
414 Page 34	401 Page 35	438 Page 36	428 Page 37
			
429 Page 38	419 Page 39	408 Page 40	

Savigny Oddie Limited

...one stop shop for all your hardware requirements



Cabinet Hinges - Medium Type 605

Supplied as a two or three piece hinge.


Supplied with 2 or 3 hexagonal bolts M10 x 12 long and 20 or 3 fan washers

Type 605 - Two piece design

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
steel	zinc & passivate	bolt through	13.00	530047

Type 605 - Three piece design

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
steel	zinc & passivate	bolt through	20.00	530048



Cabinet Hinges Medium 605

Tel: 01384 481598


Fax: 01384 482383

www.savigny-oddie.co.uk


Savigny Oddie Limited

...one stop shop for all your hardware requirements

Mounting example



Panel preparation: hole size



Cabinet Hinges Medium 605 Mounting Examples


Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk


Savigny Oddie Limited

...one stop shop for all your hardware requirements



Cabinet Hinges - Medium Type 406

Diameter of holes is 4.2mm.
The pin is riveted at both ends.



Savigny Oddie Limited

...one stop shop for all your hardware requirements

406A No Holes

Material	Finish	Nominal Weight Kg/100	Part Number
Steel	None	2.220	380237
18/8 Stainless Steel	None	2.220	380238

406 Five Holes

Material	Finish	Nominal Weight Kg/100	Part Number
Steel	None	2.140	380239
Steel	Zinc & Passivate	2.140	380241
18/8 Stainless Steel	None	2.140	380240

406E Four Holes

Material	Finish	Nominal Weight Kg/100	Part Number
Steel	None	2.140	530055
Steel	Zinc & Passivate	2.140	530056
18/8 Stainless Steel	None	2.140	530057

406F Two Holes and Elongated Slot


Material	Finish	Nominal Weight Kg/100	Part Number
Steel	None	2.140	530058
Steel	Zinc & Passivate	2.140	530059
18/8 Stainless Steel	None	2.140	530060

406G One Hole and Elongated Slot

Material	Finish	Nominal Weight Kg/100	Part Number
Steel	None	2.140	530061
Steel	Zinc & Passivate	2.140	530062
18/8 Stainless Steel	None	2.140	530063


Savigny Oddie Limited

...one stop shop for all your hardware requirements



Cabinet Hinges - Medium Type 405

Diameter of holes is 4.2mm.
The pin is riveted over at both ends.



405A - No Holes

Material	Finish	Nominal Weight Kg/100	Part Number
Steel	None	3.000	380225
18/8 Stainless Steel	None	3.000	380226

405B - Six Pierced Holes

Material	Finish	Nominal Weight Kg/100	Part Number
Steel	None	2.910	380228
Steel	Zinc & Passivate	2.910	380230
18/8 Stainless Steel	None	2.910	380229

Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk

Savigny Oddie Limited

...one stop shop for all your hardware requirements

405E - Three Pierced Holes and One Elongated Slot


Material	Finish	Nominal Weight Kg/100	Part Number
Steel	None	2.800	530049
Steel	Zinc & Passivate	2.800	530050
18/8 Stainless Steel	None	2.800	530051

405F - Two Elongated Slots

Material	Finish	Nominal Weight Kg/100	Part Number
Steel	None	2.750	530052
Steel	Zinc & Passivate	2.750	530053
18/8 Stainless Steel	None	2.750	530054

Savigny Oddie Limited


...one stop shop for all your hardware requirements



Cabinet Hinges - Medium Type 403

Bridge feature allows for protruding container edges

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
steel	zinc plate	holes	3.50	530037




Tel: 01384 481598

Fax: 01384 482383


www.savigny-oddie.co.uk

Savigny Oddie Limited

...one stop shop for all your hardware requirements



Cabinet Hinges - Medium Type 414




Type 414

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
Steel	None	Holes	3.520	380269


Savigny Oddie Limited

...one stop shop for all your hardware requirements



Cabinet Hinges - Medium Type 401

Bridge feature allows for protruding container edges.



Type 401

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
steel	zinc plate	holes	5.00	530036

Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk




Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
Steel	Zinc & Colour Passivate	Holes	3.70	380628
Stainless 18/8	None	Holes	3.70	380629



Savigny Oddie Limited


...one stop shop for all your hardware requirements



Cabinet Hinges - Medium Type 428

Type 428 - as 429 but flat

Material	Fixing	Nominal Weight Kg/100	Part Number
steel, zinc and passivate plated	CSK Holes	5.275	380294



Tel: 01384 481598


Fax: 01384 482383

www.savigny-oddie.co.uk

Savigny Oddie Limited


...one stop shop for all your hardware requirements

Cabinet Hinges - Medium Type 429



Type 429

Material	Fixing	Nominal Weight Kg/100	Part Number
steel, zinc and passivate plated	CSK Holes	6.475	380291




Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk

Savigny Oddie Limited


...one stop shop for all your hardware requirements



Cabinet Hinges - Medium Type 419

Type 419

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
Steel	Zinc Plate	Holes	3.400	380462




Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk

Savigny Oddie Limited

...one stop shop for all your hardware requirements




Cabinet Hinges - Medium Type 408

The movement of the hinge is limited to slightly over 180°
The pin is made from 18/8 stainless steel in all cases except for unplated steel item.
The pin is riveted at both ends.

Type 408

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
Steel	None	Holes	3.300	380202
Steel	Zinc & Passivate	Holes	3.300	380125
18/8 Stainless Steel	None	No Holes	3.390	380201
18/8 Stainless Steel	None	Holes	3.300	380203



Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk







Savigny Oddie Limited

...one stop shop for all your hardware requirements

Cabinet Hinges - Small


Contents

Cabinet Hinges - Small


			
416 Page 42	404 Page 43	425 Page 45	424 Page 46
			
415 Page 47	420 Page 48		

Savigny Oddie Limited

...one stop shop for all your hardware requirements



Cabinet Hinges - Small Type 416




Type 416

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
Steel	None	CSK holes	0.480	380281


Savigny Oddie Limited

...one stop shop for all your hardware requirements



Cabinet Hinges - Small Type 404

Diameter of Holes is 4.2mm.
The Pin is riveted over at both ends.



404A - No Holes

Material	Finish	Nominal Weight kg/100	Part Number
Steel	None	1.450	380211
18/8 Stainless Steel	None	1.450	380212

Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk

Savigny Oddie Limited

...one stop shop for all your hardware requirements

404B - Four Holes

Material	Finish	Nominal Weight kg/100	Part Number
Steel	None	1.390	380214
Steel	zinc & passivate	1.390	380218
18/8 Stainless Steel	None	1.390	380216

404E - Three Holes

Material	Finish	Nominal Weight kg/100	Part Number
Steel	None	1.410	530064
Steel	zinc & passivate	1.410	530065
18/8 Stainless Steel	None	1.410	530066


404F - Two Holes

Material	Finish	Nominal Weight kg/100	Part Number
Steel	None	1.430	530067
Steel	zinc & passivate	1.430	530068
18/8 Stainless Steel	None	1.430	530069

Savigny Oddie Limited


...one stop shop for all your hardware requirements

Cabinet Hinges - Small Type 425



Type 425

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
Steel	Zinc & Colour Passivate	Holes	0.70	380626
Stainless 18/8	None	Holes	0.70	380627




Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk

Savigny Oddie Limited


...one stop shop for all your hardware requirements



Cabinet Hinges - Small Type 424

Type 424

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
Steel	Zinc & Colour Passivate	Holes	1.555	380624
Stainless 18/8	None	Holes	1.555	380625




Tel: 01384 481598

Fax: 01384 482383


www.savigny-oddie.co.uk

Savigny Oddie Limited

...one stop shop for all your hardware requirements



Cabinet Hinges - Small Type 415




Type 415

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
Steel	Zinc & Passivate	Holes	1.000	380276

Savigny Oddie Limited

...one stop shop for all your hardware requirements





Cabinet Hinges - Small Type 420

The pin for type 420 is stainless steel in both cases and is riveted at both ends.

Type 420

Material	Finish	Fixing	Nominal Weight Kg/100	Part Number
Steel	Zinc & Passivate	Holes	1.700	380322
18/8 Stainless	None	Holes	1.700	380323



Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk

Savigny Oddie Limited

...one stop shop for all your hardware requirements

Made to Order Hinges





Made to Order Hinges.

Within the parameters given in the tables below we can manufacture hinges to your design at little or no tooling cost, from our standard adjustable tooling. Please give us your order quantity, the model number and type, dimensions and material / finish and we will be pleased to quote.

As an example please provide the following:

Quantity:	1,000pieces
Model Number:	410, type E
Dimensions:	A=50, B=100, E=4.2, F=33, G=75
Knuckle style:	flat
Pin Style:	1
Material / Finish:	Steel / Zinc Plate








For other special hinges with cranked leaves or other options please send us your drawing.

	
410 Page 50	480 Page 52

Savigny Oddie Limited

...one stop shop for all your hardware requirements

Model 410



Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk

Savigny Oddie Limited

...one stop shop for all your hardware requirements

Specifications: (all made to order hinges have the following variables)

Material: Steel, Stainless Steel and Light Alloy

Finish: natural, zinc and colour passivate, zinc plate

Knuckle Style: flat or offset

Dimensions							
A	B	C	D	E	F	G	H
40 to 80	your measure	1.5	4	your measure	your measure	your measure	your measure
25 to 75	your measure	2	4	your measure	your measure	your measure	your measure
40 to 80	your measure	2	5	your measure	your measure	your measure	your measure
40 to 80	your measure	2.5	5	your measure	your measure	your measure	your measure
40 to 80	your measure	2.5	6	your measure	your measure	your measure	your measure
40 to 80	your measure	3	6	your measure	your measure	your measure	your measure
45 to 115	your measure	3	10	your measure	your measure	your measure	your measure
45 to 115	your measure	5	10	your measure	your measure	your measure	your measure
45 to 115	your measure	6	12	your measure	your measure	your measure	your measure

Tel: 01384 481598









Fax: 01384 482383

www.savigny-oddie.co.uk

Savigny Oddie Limited

...one stop shop for all your hardware requirements

Model 480




Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk

Savigny Oddie Limited

...one stop shop for all your hardware requirements



Specifications: (all made to order hinges have the following variables)

Material: Steel, Stainless Steel and Light Alloy

Finish: natural, zinc and colour passivate, zinc plate

Knuckle Style: flat or offset

Dimensions										
A	B	C	D	E	F	G	H	I	J	K
40 to 80	your measure	1.5	4	your measure	your measure	your measure	your measure	your measure	your measure	your measure
25 to 75	your measure	2	4	your measure	your measure	your measure	your measure	your measure	your measure	your measure
40 to 80	your measure	2	5	your measure	your measure	your measure	your measure	your measure	your measure	your measure
40 to 80	your measure	2.5	5	your measure	your measure	your measure	your measure	your measure	your measure	your measure
40 to 80	your measure	2.5	6	your measure	your measure	your measure	your measure	your measure	your measure	your measure
40 to 80	your measure	3	6	your measure	your measure	your measure	your measure	your measure	your measure	your measure
45 to 115	your measure	3	10	your measure	your measure	your measure	your measure	your measure	your measure	your measure
45 to 115	your measure	5	10	your measure	your measure	your measure	your measure	your measure	your measure	your measure
45 to 115	your measure	5	12	your measure	your measure	your measure	your measure	your measure	your measure	your measure

Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk


Savigny Oddie Limited

...one stop shop for all your hardware requirements




654 Plastic Hinges

Supplied with either holes for bolts or with insert molded studs.
Manufactured from black polycarbonate with stainless steel pins.



With Fixing Holes

Dimensions								Nominal Weight kg/100	Part Number
A	C	H	S	d	D	D1	T		
40	25	9.0	5.0	4.0	10.5	5.3	2.5	1.5	530022
50	30	11.5	6.0	6.0	12.5	6.4	3.0	2.0	530023
60	36	15.0	8.0	8.0	16.5	8.5	3.7	3.0	530024



With Insert Moulded Studs

Dimensions							Nominal Weight kg/100	Part Number
A	C	H	S	d	M	L		
40	25	9.0	5.0	4.0	M5	12	2.2	530025
50	30	11.5	6.0	6.0	M6	12	2.7	530026
60	36	15.0	8.0	8.0	M8	14	3.7	530027

Tel: 01384 481598

Fax: 01384 482383

www.savigny-oddie.co.uk