

Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	2/0 AWG
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric
Wire Strip Length	1-1/16 in.
Stud Size	3/8 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	BLACK
Panduit Die Index No. on Barrel	P45
Alternate Industry Die Index No. () on Barrel	(13)

						 PANDUIT CORP. TINLEY PARK, ILLINOIS LCD2/0-38DF-X Copper Lug - Two-Hole, Standard Barrel, 90° Angle Tongue
01	4/04	DRL	DRL	ADDED UL, CSA & PART NO. TO STAMP	11695	
REV	DATE	BY	CHK	DESCRIPTION	ECN	
						SCALE N/A DRAWING NO / CAD FILE LCD2_0-38DF-CUST