

REV. K

DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED	TOLERANCES ARE:	ANGLES	TITLE:	DWG NO:
ONE PLACE DECIMALS: $\pm .1$	[2.5]	THREE PLACE DECIMALS: $\pm .005$	[.127]	$\pm 2^\circ$	.100 [2.54] C.L. SHUNT ASSEMBLY	SNT-100-XX-X-X
TWO PLACE DECIMALS: $\pm .01$	[.25]	FOUR PLACE DECIMALS: $\pm .0020$	[.0508]			SHEET 1 OF 1

BODY: USE SNT-100-XX
CONTACT: USE C-37-X

SNT-100-XX-X-X

OPTION
-H: HANDLE (SEE -H OPTION)

PLATING SPECIFICATION

-T = TIN: SPECIFY -T IN CONTACT SUFFIX -X
-G = GOLD: SPECIFY -G IN CONTACT SUFFIX -X
-H = HEAVY GOLD: SPECIFY -H IN CONTACT SUFFIX -X

COLOR SPECIFICATION

SPECIFY COLOR IN BODY SUFFIX -XX


BK = BLACK
RD = RED
BL = BLUE
YW = YELLOW
OR = ORANGE

CRITICAL DIMENSION INSPECTION TABLE

ASSEMBLY OPERATION	IN-PROCESS INSPECTION
FILL	C1, C2

NOTES:

1.  REPRESENTS A CRITICAL DIMENSION.
2. ALTERNATE VENDOR CAVITY ID RUNNER/CAVITY (EX: AC IS RUNNER 1 CAVITY 3).




Do not scale
from this print

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SANTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE WRITTEN
CONSENT OF SANTEC INC.

-H OPTION



BODY: USE SNH-100-XX
CONTACT: USE C-37-X

SCALE: .3

santec

MISC/MKTG
SNT-MKT

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: KOLB 1-31-90

SNT-100-XX-X-X
SHEET 1 OF 1