



Home> Products > Stainless Steel Media Isolated> Eclipse > Product Page

EC100PS1PG



Actual product appearance may vary.

Eclipse Series Stainless Steel Pressure Sensor, Amplified Output, Sealed Gage, 0 psi to 100 psi, Item Number 9253501

Features

- Voltage or current output
- 15 PSIG through 7100 PSIS ranges
- CE versions available
- High performance at low price
- Weatherproof type connector
- Reverse-polarity protection
- Low -excitation voltage
- Flexibility for the designer
- Suitable for many applications
- Ready for Europe
- Reduces OEM system cost
- High reliability and user flexibility
- Not damaged by reversed wiring
- Suitable for ORV or marine use
- Complete environmental protection for electronics

Potential Applications

- Energy management: "smart" compressors, refrigeration/ chiller control
- Hydraulic / pneumatic controls
- Automotive air compressors
- Off road vehicles

Description

The Eclipse is designed for high-volume OEM's needing a lowcost pressure transmitter for industrial or other heavy-duty applications. The Eclipse's combination of rugged packaging, internal signalamplification and price make it ideal for many applications. The pressure media is contained by a brazed assembly of stainless steel. There are no hidden O-rings or elastomers containing the media. A plated steel case protects the internal electronics. It is available with either a 0.5 Volt to 4.5 volt or 4 mA to 20 mA output. The 4 mA to 20 mA output is useful for applications where electrical noise may be a concern. Units with the Hirschmann connectors are CE approved.

Supporting Documentation

-  [Dimensions and Circuitry](#)
-  [Documentation](#)

Product Specifications	
Measurement Type	Sealed Gage
Signal Conditioning	Amplified
Pressure Range	0 psi to 100 psi
Supply Voltage	10.0 Vdc to 40.0 Vdc
Maximum Overpressure	150 psi
Burst Pressure	500 psi
Port Style	1/8 - 27 NPT
Temperature Compensation	Yes
Output Type	4 mA to 20 mA
Protection Circuitry	Reverse Polarity
Accuracy	0.25% full scale BFSL
Response Time	less than 1.0 ms
Insulation Resistance	1000 Mohms @ 50 Vdc max.
Output Calibration	Yes
Termination Type	Packard Metri - Pack™ Connector
Weight	85 grams [3.0 ounces]
Full Scale Span	16 mA
Operating Temperature Range	- 40 °C to 105 °C [- 40 °F to 221 °F]
Compensated Temperature Range	- 1 °C to 82 °C [30 °F to 180 °F]
Storage Temperature Range	NO IDEA SHARED FORMULA EXP PTG
Media Compatibility	Limited only to those media which will not attack a brazed assembly of 300 Series stainless steel parts
Approvals	CE, ULc, AGA, CSA
UNSPSC Code	411121
UNSPSC Commodity	411121 Transducers
Availability	Global
Series Name	Eclipse

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Contr▼

Product Search

Part number search:

Use (*) to expand search

Specification Search