

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200860171

Status:

Active

Overview:

Brad Nano-Change (M8) Products

Description:

Nano-Change (M8) Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 24 AWG, PUR Cable, 2.0m (6.56') Length



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
UL	E152210
General	
Product Family	Industrial Cordsets
Series	120086
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Nano-Change (M8) Products
Product Name	Nano-Change (M8)
Region	America
Type	Single Ended
UPC	78678833009
Physical	
Cable Diameter	4.57mm (.180")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Yellow
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	A-coded
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	TPE
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-25°C to +80°C
Wire Size AWG	24
Wire/Cable Type	E152210
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC / 75V DC
Material Info	
Engineering Number	404000B09M020
Reference - Drawing Numbers	
Sales Drawing	SD-120086-017

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120086 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION