

Part 1539-32K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	6.8 μ H	
Tolerance	± 10	
Q		
SRF	55 MHz	
DCR	0.55 Ω	
Max Current	432 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-06H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.47 μ H	
Tolerance	± 3	
Q		
SRF	275 MHz	
DCR	0.12 Ω	
Max Current	1370 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-07J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.56 μ H	
Tolerance	± 5	
Q		
SRF	250 MHz	
DCR	0.135 Ω	
Max Current	1290 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-06K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.47 μ H	
Tolerance	± 10	
Q		
SRF	275 MHz	
DCR	0.12 Ω	
Max Current	1370 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-06M		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.47 μ H	
Tolerance	± 20	
Q		
SRF	275 MHz	
DCR	0.12 Ω	
Max Current	1370 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-07F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.56 μ H	
Tolerance	± 1	
Q		
SRF	250 MHz	
DCR	0.135 Ω	
Max Current	1290 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-07G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.56 μ H	
Tolerance	± 2	
Q		
SRF	250 MHz	
DCR	0.135 Ω	
Max Current	1290 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-07H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.56 μ H	
Tolerance	± 3	
Q		
SRF	250 MHz	
DCR	0.135 Ω	
Max Current	1290 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-06J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.47 μ H	
Tolerance	± 5	
Q		
SRF	275 MHz	
DCR	0.12 Ω	
Max Current	1370 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-07K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.56 μ H	
Tolerance	± 10	
Q		
SRF	250 MHz	
DCR	0.135 Ω	
Max Current	1290 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-10J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.82 μ H	
Tolerance	± 5	
Q		
SRF	220 MHz	
DCR	0.22 Ω	
Max Current	1020 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-08G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.68 μ H	
Tolerance	± 2	
Q		
SRF	235 MHz	
DCR	0.15 Ω	
Max Current	1220 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-08J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.68 μ H	
Tolerance	± 5	
Q		
SRF	235 MHz	
DCR	0.15 Ω	
Max Current	1220 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-08K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.68 μ H	
Tolerance	± 10	
Q		
SRF	235 MHz	
DCR	0.15 Ω	
Max Current	1220 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-10G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.82 μ H	
Tolerance	± 2	
Q		
SRF	220 MHz	
DCR	0.22 Ω	
Max Current	1020 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-10H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.82 μ H	
Tolerance	± 3	
Q		
SRF	220 MHz	
DCR	0.22 Ω	
Max Current	1020 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-06G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.47 μ H	
Tolerance	± 2	
Q		
SRF	275 MHz	
DCR	0.12 Ω	
Max Current	1370 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-00H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.15 μ H	
Tolerance	± 3	
Q		
SRF	475 MHz	
DCR	0.03 Ω	
Max Current	2740 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-10F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.82 μ H	
Tolerance	± 1	
Q		
SRF	220 MHz	
DCR	0.22 Ω	
Max Current	1020 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-02K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.22 μ H	
Tolerance	± 10	
Q		
SRF	400 MHz	
DCR	0.055 Ω	
Max Current	2020 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-08H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.68 μ H	
Tolerance	± 3	
Q		
SRF	235 MHz	
DCR	0.15 Ω	
Max Current	1220 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-00F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.15 μ H	
Tolerance	± 1	
Q		
SRF	475 MHz	
DCR	0.03 Ω	
Max Current	2740 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-00G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.15 μ H	
Tolerance	± 2	
Q		
SRF	475 MHz	
DCR	0.03 Ω	
Max Current	2740 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-00J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.15 μ H	
Tolerance	± 5	
Q		
SRF	475 MHz	
DCR	0.03 Ω	
Max Current	2740 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-00M		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.15 μ H	
Tolerance	± 20	
Q		
SRF	475 MHz	
DCR	0.03 Ω	
Max Current	2740 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-02F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.22 μ H	
Tolerance	± 1	
Q		
SRF	400 MHz	
DCR	0.055 Ω	
Max Current	2020 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-02G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.22 μ H	
Tolerance	± 2	
Q		
SRF	400 MHz	
DCR	0.055 Ω	
Max Current	2020 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-00K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.15 μ H	
Tolerance	± 10	
Q		
SRF	475 MHz	
DCR	0.03 Ω	
Max Current	2740 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-02J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.22 μ H	
Tolerance	± 5	
Q		
SRF	400 MHz	
DCR	0.055 Ω	
Max Current	2020 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-06F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.47 μ H	
Tolerance	± 1	
Q		
SRF	275 MHz	
DCR	0.12 Ω	
Max Current	1370 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-02M		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.22 μ H	
Tolerance	± 20	
Q		
SRF	400 MHz	
DCR	0.055 Ω	
Max Current	2020 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-04F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.33 μ H	
Tolerance	± 1	
Q		
SRF	325 MHz	
DCR	0.09 Ω	
Max Current	1580 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-04G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.33 μ H	
Tolerance	± 2	
Q		
SRF	325 MHz	
DCR	0.09 Ω	
Max Current	1580 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-04H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.33 μ H	
Tolerance	± 3	
Q		
SRF	325 MHz	
DCR	0.09 Ω	
Max Current	1580 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-04J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.33 μ H	
Tolerance	± 5	
Q		
SRF	325 MHz	
DCR	0.09 Ω	
Max Current	1580 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-04K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.33 μ H	
Tolerance	± 10	
Q		
SRF	325 MHz	
DCR	0.09 Ω	
Max Current	1580 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-04M		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.33 μ H	
Tolerance	± 20	
Q		
SRF	325 MHz	
DCR	0.09 Ω	
Max Current	1580 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-02H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.22 μ H	
Tolerance	± 3	
Q		
SRF	400 MHz	
DCR	0.055 Ω	
Max Current	2020 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-64H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	56 μ H	
Tolerance	± 3	
Q		
SRF	10.5 MHz	
DCR	3.5 Ω	
Max Current	171 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-58J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	43 μ H	
Tolerance	± 5	
Q		
SRF	12.9 MHz	
DCR	2.95 Ω	
Max Current	186 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-60F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	47 μ H	
Tolerance	± 1	
Q		
SRF	12.6 MHz	
DCR	3.1 Ω	
Max Current	182 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-60G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	47 μ H	
Tolerance	± 2	
Q		
SRF	12.6 MHz	
DCR	3.1 Ω	
Max Current	182 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-60H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	47 μ H	
Tolerance	± 3	
Q		
SRF	12.6 MHz	
DCR	3.1 Ω	
Max Current	182 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-60J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	47 μ H	
Tolerance	± 5	
Q		
SRF	12.6 MHz	
DCR	3.1 Ω	
Max Current	182 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-62F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	51 μ H	
Tolerance	± 1	
Q		
SRF	12 MHz	
DCR	3.3 Ω	
Max Current	176 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-62G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	51 μ H	
Tolerance	± 2	
Q		
SRF	12 MHz	
DCR	3.3 Ω	
Max Current	176 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-62H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	51 μ H	
Tolerance	± 3	
Q		
SRF	12 MHz	
DCR	3.3 Ω	
Max Current	176 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-62J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	51 μ H	
Tolerance	± 5	
Q		
SRF	12 MHz	
DCR	3.3 Ω	
Max Current	176 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-46H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	24 μ H	
Tolerance	± 3	
Q		
SRF	26 MHz	
DCR	2.6 Ω	
Max Current	199 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-64G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	56 μ H	
Tolerance	± 2	
Q		
SRF	10.5 MHz	
DCR	3.5 Ω	
Max Current	171 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Unable to Serve this Request

Site temporarily unavailable.

Connection timed out - please try again.

Part 1539-64J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	56 μ H	
Tolerance	± 5	
Q		
SRF	10.5 MHz	
DCR	3.5 Ω	
Max Current	171 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-66F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	62 μ H	
Tolerance	± 1	
Q		
SRF	10 MHz	
DCR	3.7 Ω	
Max Current	166 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-66G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	62 μ H	
Tolerance	± 2	
Q		
SRF	10 MHz	
DCR	3.7 Ω	
Max Current	166 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-66H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	62 μ H	
Tolerance	± 3	
Q		
SRF	10 MHz	
DCR	3.7 Ω	
Max Current	166 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-66J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	62 μ H	
Tolerance	± 5	
Q		
SRF	10 MHz	
DCR	3.7 Ω	
Max Current	166 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-68F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	68 μ H	
Tolerance	± 1	
Q		
SRF	9.5 MHz	
DCR	3.8 Ω	
Max Current	164 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-68G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	68 μ H	
Tolerance	± 2	
Q		
SRF	9.5 MHz	
DCR	3.8 Ω	
Max Current	164 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-68H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	68 μ H	
Tolerance	± 3	
Q		
SRF	9.5 MHz	
DCR	3.8 Ω	
Max Current	164 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-68J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	68 μ H	
Tolerance	± 5	
Q		
SRF	9.5 MHz	
DCR	3.8 Ω	
Max Current	164 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-70F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	75 μ H	
Tolerance	± 1	
Q		
SRF	9.3 MHz	
DCR	4.3 Ω	
Max Current	154 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-64F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	56 μ H	
Tolerance	± 1	
Q		
SRF	10.5 MHz	
DCR	3.5 Ω	
Max Current	171 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-52H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	33 μ H	
Tolerance	± 3	
Q		
SRF	17.5 MHz	
DCR	3 Ω	
Max Current	185 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-46J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	24 μ H	
Tolerance	± 5	
Q		
SRF	26 MHz	
DCR	2.6 Ω	
Max Current	199 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-47F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	27 μ H	
Tolerance	± 1	
Q		
SRF	22.3 MHz	
DCR	2.75 Ω	
Max Current	193 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-47G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	27 μ H	
Tolerance	± 2	
Q		
SRF	22.3 MHz	
DCR	2.75 Ω	
Max Current	193 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-47H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	27 μ H	
Tolerance	± 3	
Q		
SRF	22.3 MHz	
DCR	2.75 Ω	
Max Current	193 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-47J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	27 μ H	
Tolerance	± 5	
Q		
SRF	22.3 MHz	
DCR	2.75 Ω	
Max Current	193 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-47K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	27 μ H	
Tolerance	± 10	
Q		
SRF	22.3 MHz	
DCR	2.75 Ω	
Max Current	193 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-50F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	30 μ H	
Tolerance	± 1	
Q		
SRF	19 MHz	
DCR	2.9 Ω	
Max Current	188 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-50G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	30 μ H	
Tolerance	± 2	
Q		
SRF	19 MHz	
DCR	2.9 Ω	
Max Current	188 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-50H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	30 μ H	
Tolerance	± 3	
Q		
SRF	19 MHz	
DCR	2.9 Ω	
Max Current	188 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-50J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	30 μ H	
Tolerance	± 5	
Q		
SRF	19 MHz	
DCR	2.9 Ω	
Max Current	188 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-58H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	43 μ H	
Tolerance	± 3	
Q		
SRF	12.9 MHz	
DCR	2.95 Ω	
Max Current	186 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-52G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	33 μ H	
Tolerance	± 2	
Q		
SRF	17.5 MHz	
DCR	3 Ω	
Max Current	185 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-58G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	43 μ H	
Tolerance	± 2	
Q		
SRF	12.9 MHz	
DCR	2.95 Ω	
Max Current	186 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-52J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	33 μ H	
Tolerance	± 5	
Q		
SRF	17.5 MHz	
DCR	3 Ω	
Max Current	185 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-54F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	36 μ H	
Tolerance	± 1	
Q		
SRF	15.5 MHz	
DCR	2.85 Ω	
Max Current	190 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-54G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	36 μ H	
Tolerance	± 2	
Q		
SRF	15.5 MHz	
DCR	2.85 Ω	
Max Current	190 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-54H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	36 μ H	
Tolerance	± 3	
Q		
SRF	15.5 MHz	
DCR	2.85 Ω	
Max Current	190 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-54J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	36 μ H	
Tolerance	± 5	
Q		
SRF	15.5 MHz	
DCR	2.85 Ω	
Max Current	190 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-56F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	39 μ H	
Tolerance	± 1	
Q		
SRF	13.8 MHz	
DCR	2.9 Ω	
Max Current	188 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-56G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	39 μ H	
Tolerance	± 2	
Q		
SRF	13.8 MHz	
DCR	2.9 Ω	
Max Current	188 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-56H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	39 μ H	
Tolerance	± 3	
Q		
SRF	13.8 MHz	
DCR	2.9 Ω	
Max Current	188 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-56J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	39 μ H	
Tolerance	± 5	
Q		
SRF	13.8 MHz	
DCR	2.9 Ω	
Max Current	188 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-70J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	75 μ H	
Tolerance	± 5	
Q		
SRF	9.3 MHz	
DCR	4.3 Ω	
Max Current	154 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-52F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	33 μ H	
Tolerance	± 1	
Q		
SRF	17.5 MHz	
DCR	3 Ω	
Max Current	185 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-90H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	200 μ H	
Tolerance	± 3	
Q		
SRF	5.9 MHz	
DCR	8 Ω	
Max Current	113 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-70G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	75 μ H	
Tolerance	± 2	
Q		
SRF	9.3 MHz	
DCR	4.3 Ω	
Max Current	154 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-84J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	150 μ H	
Tolerance	± 5	
Q		
SRF	7.1 MHz	
DCR	6.8 Ω	
Max Current	123 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-86F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	160 μ H	
Tolerance	± 1	
Q		
SRF	7 MHz	
DCR	6.9 Ω	
Max Current	122 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-86G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	160 μ H	
Tolerance	± 2	
Q		
SRF	7 MHz	
DCR	6.9 Ω	
Max Current	122 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-86H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	160 μ H	
Tolerance	± 3	
Q		
SRF	7 MHz	
DCR	6.9 Ω	
Max Current	122 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-86J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	160 μ H	
Tolerance	± 5	
Q		
SRF	7 MHz	
DCR	6.9 Ω	
Max Current	122 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-88F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	180 μ H	
Tolerance	± 1	
Q		
SRF	6.5 MHz	
DCR	7.6 Ω	
Max Current	116 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-88G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	180 μ H	
Tolerance	± 2	
Q		
SRF	6.5 MHz	
DCR	7.6 Ω	
Max Current	116 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-88H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	180 μ H	
Tolerance	± 3	
Q		
SRF	6.5 MHz	
DCR	7.6 Ω	
Max Current	116 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-88J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	180 μ H	
Tolerance	± 5	
Q		
SRF	6.5 MHz	
DCR	7.6 Ω	
Max Current	116 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-84G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	150 μ H	
Tolerance	± 2	
Q		
SRF	7.1 MHz	
DCR	6.8 Ω	
Max Current	123 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-90G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	200 μ H	
Tolerance	± 2	
Q		
SRF	5.9 MHz	
DCR	8 Ω	
Max Current	113 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-84F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	150 μ H	
Tolerance	± 1	
Q		
SRF	7.1 MHz	
DCR	6.8 Ω	
Max Current	123 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-90J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	200 μ H	
Tolerance	± 5	
Q		
SRF	5.9 MHz	
DCR	8 Ω	
Max Current	113 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-92F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	220 μ H	
Tolerance	± 1	
Q		
SRF	5.5 MHz	
DCR	8.5 Ω	
Max Current	110 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-92G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	220 μ H	
Tolerance	± 2	
Q		
SRF	5.5 MHz	
DCR	8.5 Ω	
Max Current	110 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-92H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	220 μ H	
Tolerance	± 3	
Q		
SRF	5.5 MHz	
DCR	8.5 Ω	
Max Current	110 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-92J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	220 μ H	
Tolerance	± 5	
Q		
SRF	5.5 MHz	
DCR	8.5 Ω	
Max Current	110 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-94F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	240 μ H	
Tolerance	± 1	
Q		
SRF	5.1 MHz	
DCR	8.8 Ω	
Max Current	108 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-94G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	240 μ H	
Tolerance	± 2	
Q		
SRF	5.1 MHz	
DCR	8.8 Ω	
Max Current	108 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-94H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	240 μ H	
Tolerance	± 3	
Q		
SRF	5.1 MHz	
DCR	8.8 Ω	
Max Current	108 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-94J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	240 μ H	
Tolerance	± 5	
Q		
SRF	5.1 MHz	
DCR	8.8 Ω	
Max Current	108 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-08F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.68 μ H	
Tolerance	± 1	
Q		
SRF	235 MHz	
DCR	0.15 Ω	
Max Current	1220 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-90F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	200 μ H	
Tolerance	± 1	
Q		
SRF	5.9 MHz	
DCR	8 Ω	
Max Current	113 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-78G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	110 μ H	
Tolerance	± 2	
Q		
SRF	8.1 MHz	
DCR	5.6 Ω	
Max Current	135 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-76H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	100 μ H	
Tolerance	± 3	
Q		
SRF	8.7 MHz	
DCR	5.3 Ω	
Max Current	139 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-72F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	82 μ H	
Tolerance	± 1	
Q		
SRF	9.2 MHz	
DCR	4.5 Ω	
Max Current	151 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-72G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	82 μ H	
Tolerance	± 2	
Q		
SRF	9.2 MHz	
DCR	4.5 Ω	
Max Current	151 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-72H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	82 μ H	
Tolerance	± 3	
Q		
SRF	9.2 MHz	
DCR	4.5 Ω	
Max Current	151 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-72J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	82 μ H	
Tolerance	± 5	
Q		
SRF	9.2 MHz	
DCR	4.5 Ω	
Max Current	151 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-74F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	91 μ H	
Tolerance	± 1	
Q		
SRF	9 MHz	
DCR	4.9 Ω	
Max Current	145 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-74G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	91 μ H	
Tolerance	± 2	
Q		
SRF	9 MHz	
DCR	4.9 Ω	
Max Current	145 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-74H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	91 μ H	
Tolerance	± 3	
Q		
SRF	9 MHz	
DCR	4.9 Ω	
Max Current	145 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-74J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	91 μ H	
Tolerance	± 5	
Q		
SRF	9 MHz	
DCR	4.9 Ω	
Max Current	145 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-76F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	100 μ H	
Tolerance	± 1	
Q		
SRF	8.7 MHz	
DCR	5.3 Ω	
Max Current	139 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-84H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	150 μ H	
Tolerance	± 3	
Q		
SRF	7.1 MHz	
DCR	6.8 Ω	
Max Current	123 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-76J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	100 μ H	
Tolerance	± 5	
Q		
SRF	8.7 MHz	
DCR	5.3 Ω	
Max Current	139 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-70H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	75 μ H	
Tolerance	± 3	
Q		
SRF	9.3 MHz	
DCR	4.3 Ω	
Max Current	154 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-78H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	110 μ H	
Tolerance	± 3	
Q		
SRF	8.1 MHz	
DCR	5.6 Ω	
Max Current	135 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-78J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	110 μ H	
Tolerance	± 5	
Q		
SRF	8.1 MHz	
DCR	5.6 Ω	
Max Current	135 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-80F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	120 μ H	
Tolerance	± 1	
Q		
SRF	7.5 MHz	
DCR	6 Ω	
Max Current	131 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-80G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	120 μ H	
Tolerance	± 2	
Q		
SRF	7.5 MHz	
DCR	6 Ω	
Max Current	131 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-80H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	120 μ H	
Tolerance	± 3	
Q		
SRF	7.5 MHz	
DCR	6 Ω	
Max Current	131 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-80J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	120 μ H	
Tolerance	± 5	
Q		
SRF	7.5 MHz	
DCR	6 Ω	
Max Current	131 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-82F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	130 μ H	
Tolerance	± 1	
Q		
SRF	7.3 MHz	
DCR	6.3 Ω	
Max Current	128 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-82G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	130 μ H	
Tolerance	± 2	
Q		
SRF	7.3 MHz	
DCR	6.3 Ω	
Max Current	128 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-82H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	130 μ H	
Tolerance	± 3	
Q		
SRF	7.3 MHz	
DCR	6.3 Ω	
Max Current	128 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-82J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	130 μ H	
Tolerance	± 5	
Q		
SRF	7.3 MHz	
DCR	6.3 Ω	
Max Current	128 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-76G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	100 μ H	
Tolerance	± 2	
Q		
SRF	8.7 MHz	
DCR	5.3 Ω	
Max Current	139 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-26F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	3.9 μ H	
Tolerance	± 1	
Q		
SRF	100 MHz	
DCR	2.45 Ω	
Max Current	305 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-20K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	2.2 μ H	
Tolerance	± 10	
Q		
SRF	135 MHz	
DCR	1.03 Ω	
Max Current	470 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-22F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	2.7 μ H	
Tolerance	± 1	
Q		
SRF	125 MHz	
DCR	1.2 Ω	
Max Current	430 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-22G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	2.7 μ H	
Tolerance	± 2	
Q		
SRF	125 MHz	
DCR	1.2 Ω	
Max Current	430 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-22H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	2.7 μ H	
Tolerance	± 3	
Q		
SRF	125 MHz	
DCR	1.2 Ω	
Max Current	430 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-22J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	2.7 μ H	
Tolerance	± 5	
Q		
SRF	125 MHz	
DCR	1.2 Ω	
Max Current	430 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-22K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	2.7 μ H	
Tolerance	± 10	
Q		
SRF	125 MHz	
DCR	1.2 Ω	
Max Current	430 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-24F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	3.3 μ H	
Tolerance	± 1	
Q		
SRF	110 MHz	
DCR	2 Ω	
Max Current	335 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-24G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	3.3 μ H	
Tolerance	± 2	
Q		
SRF	110 MHz	
DCR	2 Ω	
Max Current	335 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-24H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	3.3 μ H	
Tolerance	± 3	
Q		
SRF	110 MHz	
DCR	2 Ω	
Max Current	335 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-28G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	4.7 μ H	
Tolerance	± 2	
Q		
SRF	90 MHz	
DCR	2.6 Ω	
Max Current	294 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-24K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	3.3 μ H	
Tolerance	± 10	
Q		
SRF	110 MHz	
DCR	2 Ω	
Max Current	335 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-20G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	2.2 μ H	
Tolerance	± 2	
Q		
SRF	135 MHz	
DCR	1.03 Ω	
Max Current	470 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-26G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	3.9 μ H	
Tolerance	± 2	
Q		
SRF	100 MHz	
DCR	2.45 Ω	
Max Current	305 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-26H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	3.9 μ H	
Tolerance	± 3	
Q		
SRF	100 MHz	
DCR	2.45 Ω	
Max Current	305 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-26J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	3.9 μ H	
Tolerance	± 5	
Q		
SRF	100 MHz	
DCR	2.45 Ω	
Max Current	305 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-26K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	3.9 μ H	
Tolerance	± 10	
Q		
SRF	100 MHz	
DCR	2.45 Ω	
Max Current	305 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-27F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	4.3 μ H	
Tolerance	± 1	
Q		
SRF	95 MHz	
DCR	2.5 Ω	
Max Current	300 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-27G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	4.3 μ H	
Tolerance	± 2	
Q		
SRF	95 MHz	
DCR	2.5 Ω	
Max Current	300 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-27H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	4.3 μ H	
Tolerance	± 3	
Q		
SRF	95 MHz	
DCR	2.5 Ω	
Max Current	300 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-27J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	4.3 μ H	
Tolerance	± 5	
Q		
SRF	95 MHz	
DCR	2.5 Ω	
Max Current	300 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-27K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	4.3 μ H	
Tolerance	± 10	
Q		
SRF	95 MHz	
DCR	2.5 Ω	
Max Current	300 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-28F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	4.7 μ H	
Tolerance	± 1	
Q		
SRF	90 MHz	
DCR	2.6 Ω	
Max Current	294 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-24J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	3.3 μ H	
Tolerance	± 5	
Q		
SRF	110 MHz	
DCR	2 Ω	
Max Current	335 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-14K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1.2 μ H	
Tolerance	± 10	
Q		
SRF	180 MHz	
DCR	0.48 Ω	
Max Current	685 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-78F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	110 μ H	
Tolerance	± 1	
Q		
SRF	8.1 MHz	
DCR	5.6 Ω	
Max Current	135 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-46G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	24 μ H	
Tolerance	± 2	
Q		
SRF	26 MHz	
DCR	2.6 Ω	
Max Current	199 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-12F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1 μ H	
Tolerance	± 1	
Q		
SRF	200 MHz	
DCR	0.29 Ω	
Max Current	880 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-12G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1 μ H	
Tolerance	± 2	
Q		
SRF	200 MHz	
DCR	0.29 Ω	
Max Current	880 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-12H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1 μ H	
Tolerance	± 3	
Q		
SRF	200 MHz	
DCR	0.29 Ω	
Max Current	880 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-12J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1 μ H	
Tolerance	± 5	
Q		
SRF	200 MHz	
DCR	0.29 Ω	
Max Current	880 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-12K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1 μ H	
Tolerance	± 10	
Q		
SRF	200 MHz	
DCR	0.29 Ω	
Max Current	880 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-10K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	0.82 μ H	
Tolerance	± 10	
Q		
SRF	220 MHz	
DCR	0.22 Ω	
Max Current	1020 mA	
Inc Current		
Inc Current %		
Ind Test Freq	4 MHz	
Q Test Freq	4 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-14F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1.2 μ H	
Tolerance	± 1	
Q		
SRF	180 MHz	
DCR	0.48 Ω	
Max Current	685 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-14G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1.2 μ H	
Tolerance	± 2	
Q		
SRF	180 MHz	
DCR	0.48 Ω	
Max Current	685 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-20J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	2.2 μ H	
Tolerance	± 5	
Q		
SRF	135 MHz	
DCR	1.03 Ω	
Max Current	470 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-14J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1.2 μ H	
Tolerance	± 5	
Q		
SRF	180 MHz	
DCR	0.48 Ω	
Max Current	685 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-20H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	2.2 μ H	
Tolerance	± 3	
Q		
SRF	135 MHz	
DCR	1.03 Ω	
Max Current	470 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-16F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1.5 μ H	
Tolerance	± 1	
Q		
SRF	160 MHz	
DCR	0.55 Ω	
Max Current	650 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-16G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1.5 μ H	
Tolerance	± 2	
Q		
SRF	160 MHz	
DCR	0.55 Ω	
Max Current	650 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-16H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1.5 μ H	
Tolerance	± 3	
Q		
SRF	160 MHz	
DCR	0.55 Ω	
Max Current	650 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-16J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1.5 μ H	
Tolerance	± 5	
Q		
SRF	160 MHz	
DCR	0.55 Ω	
Max Current	650 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-16K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1.5 μ H	
Tolerance	± 10	
Q		
SRF	160 MHz	
DCR	0.55 Ω	
Max Current	650 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-18F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1.8 μ H	
Tolerance	± 1	
Q		
SRF	150 MHz	
DCR	0.65 Ω	
Max Current	590 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-18G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1.8 μ H	
Tolerance	± 2	
Q		
SRF	150 MHz	
DCR	0.65 Ω	
Max Current	590 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-18J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1.8 μ H	
Tolerance	± 5	
Q		
SRF	150 MHz	
DCR	0.65 Ω	
Max Current	590 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-20F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	2.2 μ H	
Tolerance	± 1	
Q		
SRF	135 MHz	
DCR	1.03 Ω	
Max Current	470 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-18K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1.8 μ H	
Tolerance	± 10	
Q		
SRF	150 MHz	
DCR	0.65 Ω	
Max Current	590 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-14H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1.2 μ H	
Tolerance	± 3	
Q		
SRF	180 MHz	
DCR	0.48 Ω	
Max Current	685 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-42G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	18 μ H	
Tolerance	± 2	
Q		
SRF	34 MHz	
DCR	2.37 Ω	
Max Current	208 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-36H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	10 μ H	
Tolerance	± 3	
Q		
SRF	45 MHz	
DCR	1 Ω	
Max Current	320 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-36J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	10 μ H	
Tolerance	± 5	
Q		
SRF	45 MHz	
DCR	1 Ω	
Max Current	320 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-36K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	10 μ H	
Tolerance	± 10	
Q		
SRF	45 MHz	
DCR	1 Ω	
Max Current	320 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-38F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	12 μ H	
Tolerance	± 1	
Q		
SRF	42 MHz	
DCR	1.16 Ω	
Max Current	297 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-38G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	12 μ H	
Tolerance	± 2	
Q		
SRF	42 MHz	
DCR	1.16 Ω	
Max Current	297 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-38H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	12 μ H	
Tolerance	± 3	
Q		
SRF	42 MHz	
DCR	1.16 Ω	
Max Current	297 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-38J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	12 μ H	
Tolerance	± 5	
Q		
SRF	42 MHz	
DCR	1.16 Ω	
Max Current	297 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-38K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	12 μ H	
Tolerance	± 10	
Q		
SRF	42 MHz	
DCR	1.16 Ω	
Max Current	297 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-40F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	15 μ H	
Tolerance	± 1	
Q		
SRF	37 MHz	
DCR	1.4 Ω	
Max Current	271 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-40G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	15 μ H	
Tolerance	± 2	
Q		
SRF	37 MHz	
DCR	1.4 Ω	
Max Current	271 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-36G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	10 μ H	
Tolerance	± 2	
Q		
SRF	45 MHz	
DCR	1 Ω	
Max Current	320 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-42F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	18 μ H	
Tolerance	± 1	
Q		
SRF	34 MHz	
DCR	2.37 Ω	
Max Current	208 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-40H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	15 μ H	
Tolerance	± 3	
Q		
SRF	37 MHz	
DCR	1.4 Ω	
Max Current	271 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-42H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	18 μ H	
Tolerance	± 3	
Q		
SRF	34 MHz	
DCR	2.37 Ω	
Max Current	208 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-42J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	18 μ H	
Tolerance	± 5	
Q		
SRF	34 MHz	
DCR	2.37 Ω	
Max Current	208 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-42K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	18 μ H	
Tolerance	± 10	
Q		
SRF	34 MHz	
DCR	2.37 Ω	
Max Current	208 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-44F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	22 μ H	
Tolerance	± 1	
Q		
SRF	30 MHz	
DCR	2.6 Ω	
Max Current	199 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-44G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	22 μ H	
Tolerance	± 2	
Q		
SRF	30 MHz	
DCR	2.6 Ω	
Max Current	199 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-44H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	22 μ H	
Tolerance	± 3	
Q		
SRF	30 MHz	
DCR	2.6 Ω	
Max Current	199 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-44J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	22 μ H	
Tolerance	± 5	
Q		
SRF	30 MHz	
DCR	2.6 Ω	
Max Current	199 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-28H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	4.7 μ H	
Tolerance	± 3	
Q		
SRF	90 MHz	
DCR	2.6 Ω	
Max Current	294 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-18H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	1.8 μ H	
Tolerance	± 3	
Q		
SRF	150 MHz	
DCR	0.65 Ω	
Max Current	590 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-44K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	22 μ H	
Tolerance	± 10	
Q		
SRF	30 MHz	
DCR	2.6 Ω	
Max Current	199 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-46F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	24 μ H	
Tolerance	± 1	
Q		
SRF	26 MHz	
DCR	2.6 Ω	
Max Current	199 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-40J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	15 μ H	
Tolerance	± 5	
Q		
SRF	37 MHz	
DCR	1.4 Ω	
Max Current	271 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-30J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	5.6 μ H	
Tolerance	± 5	
Q		
SRF	60 MHz	
DCR	0.37 Ω	
Max Current	526 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-28K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	4.7 μ H	
Tolerance	± 10	
Q		
SRF	90 MHz	
DCR	2.6 Ω	
Max Current	294 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-29F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	5.1 μ H	
Tolerance	± 1	
Q		
SRF	60 MHz	
DCR	0.32 Ω	
Max Current	566 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-29G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	5.1 μ H	
Tolerance	± 2	
Q		
SRF	60 MHz	
DCR	0.32 Ω	
Max Current	566 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-40K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	15 μ H	
Tolerance	± 10	
Q		
SRF	37 MHz	
DCR	1.4 Ω	
Max Current	271 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.4 MHz	
Q Test Freq	0.4 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-36F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	10 μ H	
Tolerance	± 1	
Q		
SRF	45 MHz	
DCR	1 Ω	
Max Current	320 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-29H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	5.1 μ H	
Tolerance	± 3	
Q		
SRF	60 MHz	
DCR	0.32 Ω	
Max Current	566 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-29J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	5.1 μ H	
Tolerance	± 5	
Q		
SRF	60 MHz	
DCR	0.32 Ω	
Max Current	566 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-29K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	5.1 μ H	
Tolerance	± 10	
Q		
SRF	60 MHz	
DCR	0.32 Ω	
Max Current	566 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-30F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	5.6 μ H	
Tolerance	± 1	
Q		
SRF	60 MHz	
DCR	0.37 Ω	
Max Current	526 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-28J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	4.7 μ H	
Tolerance	± 5	
Q		
SRF	90 MHz	
DCR	2.6 Ω	
Max Current	294 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Phenolic	
Sleeve	Not Applicable	

Part 1539-30H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	5.6 μ H	
Tolerance	± 3	
Q		
SRF	60 MHz	
DCR	0.37 Ω	
Max Current	526 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-30K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	5.6 μ H	
Tolerance	± 10	
Q		
SRF	60 MHz	
DCR	0.37 Ω	
Max Current	526 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-32H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	6.8 μ H	
Tolerance	± 3	
Q		
SRF	55 MHz	
DCR	0.55 Ω	
Max Current	432 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-30G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	5.6 μ H	
Tolerance	± 2	
Q		
SRF	60 MHz	
DCR	0.37 Ω	
Max Current	526 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-34J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	8.2 μ H	
Tolerance	± 5	
Q		
SRF	50 MHz	
DCR	0.63 Ω	
Max Current	403 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-34F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	8.2 μ H	
Tolerance	± 1	
Q		
SRF	50 MHz	
DCR	0.63 Ω	
Max Current	403 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-34H		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	8.2 μ H	
Tolerance	± 3	
Q		
SRF	50 MHz	
DCR	0.63 Ω	
Max Current	403 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-32J		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	6.8 μ H	
Tolerance	± 5	
Q		
SRF	55 MHz	
DCR	0.55 Ω	
Max Current	432 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-34G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	8.2 μ H	
Tolerance	± 2	
Q		
SRF	50 MHz	
DCR	0.63 Ω	
Max Current	403 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-32G		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	6.8 μ H	
Tolerance	± 2	
Q		
SRF	55 MHz	
DCR	0.55 Ω	
Max Current	432 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-32F		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	6.8 μ H	
Tolerance	± 1	
Q		
SRF	55 MHz	
DCR	0.55 Ω	
Max Current	432 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Part 1539-34K		Check Stock
Series	1539	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.375 inches	
Width	0.156 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.9 grams	
Inductance	8.2 μ H	
Tolerance	± 10	
Q		
SRF	50 MHz	
DCR	0.63 Ω	
Max Current	403 mA	
Inc Current		
Inc Current %		
Ind Test Freq	1 MHz	
Q Test Freq	1 MHz	
Core	Iron	
Sleeve	Not Applicable	

Parts

1539-00F Molded Unshielded RF Coil
 1539-00G Molded Unshielded RF Coil
 1539-00H Molded Unshielded RF Coil
 1539-00J Molded Unshielded RF Coil
 1539-00K Molded Unshielded RF Coil
 1539-00M Molded Unshielded RF Coil
 1539-02F Molded Unshielded RF Coil
 1539-02G Molded Unshielded RF Coil
 1539-02H Molded Unshielded RF Coil
 1539-02J Molded Unshielded RF Coil
 1539-02K Molded Unshielded RF Coil
 1539-02M Molded Unshielded RF Coil
 1539-04F Molded Unshielded RF Coil

1539-04G Molded Unshielded RF Coil
1539-04H Molded Unshielded RF Coil
1539-04J Molded Unshielded RF Coil
1539-04K Molded Unshielded RF Coil
1539-04M Molded Unshielded RF Coil
1539-06F Molded Unshielded RF Coil
1539-06G Molded Unshielded RF Coil
1539-06H Molded Unshielded RF Coil
1539-06J Molded Unshielded RF Coil
1539-06K Molded Unshielded RF Coil
1539-06M Molded Unshielded RF Coil
1539-07F Molded Unshielded RF Coil
1539-07G Molded Unshielded RF Coil
1539-07H Molded Unshielded RF Coil
1539-07J Molded Unshielded RF Coil
1539-07K Molded Unshielded RF Coil
1539-08F Molded Unshielded RF Coil
1539-08G Molded Unshielded RF Coil
1539-08H Molded Unshielded RF Coil
1539-08J Molded Unshielded RF Coil
1539-08K Molded Unshielded RF Coil
1539-10F Molded Unshielded RF Coil
1539-10G Molded Unshielded RF Coil
1539-10H Molded Unshielded RF Coil
1539-10J Molded Unshielded RF Coil
1539-10K Molded Unshielded RF Coil
1539-12F Molded Unshielded RF Coil
1539-12G Molded Unshielded RF Coil
1539-12H Molded Unshielded RF Coil
1539-12J Molded Unshielded RF Coil
1539-12K Molded Unshielded RF Coil
1539-14F Molded Unshielded RF Coil
1539-14G Molded Unshielded RF Coil
1539-14H Molded Unshielded RF Coil
1539-14J Molded Unshielded RF Coil
1539-14K Molded Unshielded RF Coil
1539-16F Molded Unshielded RF Coil
1539-16G Molded Unshielded RF Coil
1539-16H Molded Unshielded RF Coil
1539-16J Molded Unshielded RF Coil
1539-16K Molded Unshielded RF Coil
1539-18F Molded Unshielded RF Coil
1539-18G Molded Unshielded RF Coil
1539-18H Molded Unshielded RF Coil
1539-18J Molded Unshielded RF Coil
1539-18K Molded Unshielded RF Coil
1539-20F Molded Unshielded RF Coil
1539-20G Molded Unshielded RF Coil
1539-20H Molded Unshielded RF Coil
1539-20J Molded Unshielded RF Coil

1539-20K Molded Unshielded RF Coil
1539-22F Molded Unshielded RF Coil
1539-22G Molded Unshielded RF Coil
1539-22H Molded Unshielded RF Coil
1539-22J Molded Unshielded RF Coil
1539-22K Molded Unshielded RF Coil
1539-24F Molded Unshielded RF Coil
1539-24G Molded Unshielded RF Coil
1539-24H Molded Unshielded RF Coil
1539-24J Molded Unshielded RF Coil
1539-24K Molded Unshielded RF Coil
1539-26F Molded Unshielded RF Coil
1539-26G Molded Unshielded RF Coil
1539-26H Molded Unshielded RF Coil
1539-26J Molded Unshielded RF Coil
1539-26K Molded Unshielded RF Coil
1539-27F Molded Unshielded RF Coil
1539-27G Molded Unshielded RF Coil
1539-27H Molded Unshielded RF Coil
1539-27J Molded Unshielded RF Coil
1539-27K Molded Unshielded RF Coil
1539-28F Molded Unshielded RF Coil
1539-28G Molded Unshielded RF Coil
1539-28H Molded Unshielded RF Coil
1539-28J Molded Unshielded RF Coil
1539-28K Molded Unshielded RF Coil
1539-29F Molded Unshielded RF Coil
1539-29G Molded Unshielded RF Coil
1539-29H Molded Unshielded RF Coil
1539-29J Molded Unshielded RF Coil
1539-29K Molded Unshielded RF Coil
1539-30F Molded Unshielded RF Coil
1539-30G Molded Unshielded RF Coil
1539-30H Molded Unshielded RF Coil
1539-30J Molded Unshielded RF Coil
1539-30K Molded Unshielded RF Coil
1539-32F Molded Unshielded RF Coil
1539-32G Molded Unshielded RF Coil
1539-32H Molded Unshielded RF Coil
1539-32J Molded Unshielded RF Coil
1539-32K Molded Unshielded RF Coil
1539-34F Molded Unshielded RF Coil
1539-34G Molded Unshielded RF Coil
1539-34H Molded Unshielded RF Coil
1539-34J Molded Unshielded RF Coil
1539-34K Molded Unshielded RF Coil
1539-36F Molded Unshielded RF Coil
1539-36G Molded Unshielded RF Coil
1539-36H Molded Unshielded RF Coil
1539-36J Molded Unshielded RF Coil

1539-36K Molded Unshielded RF Coil
1539-38F Molded Unshielded RF Coil
1539-38G Molded Unshielded RF Coil
1539-38H Molded Unshielded RF Coil
1539-38J Molded Unshielded RF Coil
1539-38K Molded Unshielded RF Coil
1539-40F Molded Unshielded RF Coil
1539-40G Molded Unshielded RF Coil
1539-40H Molded Unshielded RF Coil
1539-40J Molded Unshielded RF Coil
1539-40K Molded Unshielded RF Coil
1539-42F Molded Unshielded RF Coil
1539-42G Molded Unshielded RF Coil
1539-42H Molded Unshielded RF Coil
1539-42J Molded Unshielded RF Coil
1539-42K Molded Unshielded RF Coil
1539-44F Molded Unshielded RF Coil
1539-44G Molded Unshielded RF Coil
1539-44H Molded Unshielded RF Coil
1539-44J Molded Unshielded RF Coil
1539-44K Molded Unshielded RF Coil
1539-46F Molded Unshielded RF Coil
1539-46G Molded Unshielded RF Coil
1539-46H Molded Unshielded RF Coil
1539-46J Molded Unshielded RF Coil
1539-47F Molded Unshielded RF Coil
1539-47G Molded Unshielded RF Coil
1539-47H Molded Unshielded RF Coil
1539-47J Molded Unshielded RF Coil
1539-47K Molded Unshielded RF Coil
1539-50F Molded Unshielded RF Coil
1539-50G Molded Unshielded RF Coil
1539-50H Molded Unshielded RF Coil
1539-50J Molded Unshielded RF Coil
1539-52F Molded Unshielded RF Coil
1539-52G Molded Unshielded RF Coil
1539-52H Molded Unshielded RF Coil
1539-52J Molded Unshielded RF Coil
1539-54F Molded Unshielded RF Coil
1539-54G Molded Unshielded RF Coil
1539-54H Molded Unshielded RF Coil
1539-54J Molded Unshielded RF Coil
1539-56F Molded Unshielded RF Coil
1539-56G Molded Unshielded RF Coil
1539-56H Molded Unshielded RF Coil
1539-56J Molded Unshielded RF Coil
1539-58F Molded Unshielded RF Coil
1539-58G Molded Unshielded RF Coil
1539-58H Molded Unshielded RF Coil
1539-58J Molded Unshielded RF Coil

1539-60F Molded Unshielded RF Coil
1539-60G Molded Unshielded RF Coil
1539-60H Molded Unshielded RF Coil
1539-60J Molded Unshielded RF Coil
1539-62F Molded Unshielded RF Coil
1539-62G Molded Unshielded RF Coil
1539-62H Molded Unshielded RF Coil
1539-62J Molded Unshielded RF Coil
1539-64F Molded Unshielded RF Coil
1539-64G Molded Unshielded RF Coil
1539-64H Molded Unshielded RF Coil
1539-64J Molded Unshielded RF Coil
1539-66F Molded Unshielded RF Coil
1539-66G Molded Unshielded RF Coil
1539-66H Molded Unshielded RF Coil
1539-66J Molded Unshielded RF Coil
1539-68F Molded Unshielded RF Coil
1539-68G Molded Unshielded RF Coil
1539-68H Molded Unshielded RF Coil
1539-68J Molded Unshielded RF Coil
1539-70F Molded Unshielded RF Coil
1539-70G Molded Unshielded RF Coil
1539-70H Molded Unshielded RF Coil
1539-70J Molded Unshielded RF Coil
1539-72F Molded Unshielded RF Coil
1539-72G Molded Unshielded RF Coil
1539-72H Molded Unshielded RF Coil
1539-72J Molded Unshielded RF Coil
1539-74F Molded Unshielded RF Coil
1539-74G Molded Unshielded RF Coil
1539-74H Molded Unshielded RF Coil
1539-74J Molded Unshielded RF Coil
1539-76F Molded Unshielded RF Coil
1539-76G Molded Unshielded RF Coil
1539-76H Molded Unshielded RF Coil
1539-76J Molded Unshielded RF Coil
1539-78F Molded Unshielded RF Coil
1539-78G Molded Unshielded RF Coil
1539-78H Molded Unshielded RF Coil
1539-78J Molded Unshielded RF Coil
1539-80F Molded Unshielded RF Coil
1539-80G Molded Unshielded RF Coil
1539-80H Molded Unshielded RF Coil
1539-80J Molded Unshielded RF Coil
1539-82F Molded Unshielded RF Coil
1539-82G Molded Unshielded RF Coil
1539-82H Molded Unshielded RF Coil
1539-82J Molded Unshielded RF Coil
1539-84F Molded Unshielded RF Coil
1539-84G Molded Unshielded RF Coil

1539-84H Molded Unshielded RF Coil
1539-84J Molded Unshielded RF Coil
1539-86F Molded Unshielded RF Coil
1539-86G Molded Unshielded RF Coil
1539-86H Molded Unshielded RF Coil
1539-86J Molded Unshielded RF Coil
1539-88F Molded Unshielded RF Coil
1539-88G Molded Unshielded RF Coil
1539-88H Molded Unshielded RF Coil
1539-88J Molded Unshielded RF Coil
1539-90F Molded Unshielded RF Coil
1539-90G Molded Unshielded RF Coil
1539-90H Molded Unshielded RF Coil
1539-90J Molded Unshielded RF Coil
1539-92F Molded Unshielded RF Coil
1539-92G Molded Unshielded RF Coil
1539-92H Molded Unshielded RF Coil
1539-92J Molded Unshielded RF Coil
1539-94F Molded Unshielded RF Coil
1539-94G Molded Unshielded RF Coil
1539-94H Molded Unshielded RF Coil
1539-94J Molded Unshielded RF Coil