



Wireless LAN



Product Brief Rugged Wireless LAN Serial Port Adapter 311gs

The RUGGED WIRELESS LAN SERIAL PORT ADAPTER™ 311gs is a complete wireless serial cable replacement Wireless LAN product. With its IP65-classed housing it is built for tough, demanding environments and can be installed directly in the customer's factory without any additional housing.

Key Features

- IP65-classed rugged metal housing
- RS232/422/485 interface
- 802.11b+g (54 Mbit/s) Wireless LAN version
- Long Range (20 dBm)
- Designed for high performance/throughput
- AT Command support
- Wireless Multidrop™ with up to 7 slaves
- Configuration over Wireless LAN
- WEP WPA WPA2 security software features
- Radio Type Approved for Europe, US and Canada
- Compliant with EMC, Safety and Medical standards
- Lead Free and RoHS compliant
- Only high quality components used
- External antenna with Reversed Polarity SMA connector
- Industrial and Automotive temperature range -30 - +85°C
- Individually tested and tuned in production
- Custom factory configuration possible

Technical Data

SPECIFICATIONS

Wireless LAN Support

802.11 specification

Security: Supports WEP, WPA and WPA2

PHY/MAC

802.11b and 802.11g

Extended rate protection

Regulatory domain support

Power save control

Defragmentation

Infrastructure modes

BSS

IBSS

Security

WEP64

WEP128

WPA-PSK

WPA2-PSK

TKIP

CCMP (AES)

LEAP

Software

All software including TCP/IP stack is included in the module

Configurable locally or over Wireless LAN using

AT commands or Windows Software

Serial Interface

RS232/422/485

Supported baud rates: 300 – 921.6k

Support for non-standard baud rates

Flow control: CTS/RTS or none

Housing

IP65-classed rugged aluminium box

Mounting brackets

Connectors

Male 9-pin Dsub for serial interface

Binder 712 rugged plug for power supply

Power Supply

8-30 VDC

Current Consumption

Min:TBD

Max: TBD

Dimension/Size

75.5 x 84.6 x 34.6 mm

Type Approval

R&TTE (Europe)

FCC/CFR 47 part 15 unlicensed modular transmitter approval

IC (Industrie Canada)

Environmental

Maximum operating temperature: -30 - +85 °C

Storage temperature: -40 - +85°C

Humidity RH 5-90% non-condensing

Shock and vibration: IEC 61131-2

Certifications and Compliance

R&TTE Directive 1999/5/EC

EN 300 328 V1.6.1 (2004-11)

EMC Directive: 89/336/EEC

EN 301 489-1 V1.4.1 (2002-08)

EN 301 489-17 V1.2.1 (2002-08)

EN 61000-6-2 (2001)

Safety Compliance

EN 60950-1:2001 and/or IEC 60950-1:2001 (1st Edition)

EN 60950-1/A11:2004 + Corrigendum:2004

Medical Electrical Equipment

IEC 60601-1-2 (2001)



Order Number

cB-RWSPA311gs-01

Rugged Wireless LAN Serial Port Adapter 311gs Complete Kit

Includes: RWSPA311gs-03 (External Antenna with 9-pin Dsub connector), RS-232 Cable, Binder 712 connector, mounting brackets, 10cm stub antenna, CD with Configuration Software

cB-RWSPA311gs-03

Rugged Wireless LAN Serial Port Adapter 311gs External Antenna with 9-pin Dsub connector including 10cm stub antenna

DISTRIBUTORS NEAR YOU

connectBlue

HEAD OFFICE: connectBlue AB • Norra Vallgatan 64 3v • SE-211 22 Malmö • Sweden • Phone +46 40-6307100 • Fax +46 40-237137
US OFFICE: connectBlue, Inc. • 1460 N. Sandburg Terrace, Suite 803 • Chicago, IL 60610 • USA • Phone +1 (312) 927 5859 • Fax +1 (312) 277 3209
info@connectblue.com • us-info@connectblue.com • www.connectblue.com

Printed in Sweden. ©2007 connectBlue AB. All rights reserved. All specifications are subject to change without notice.
The Bluetooth word mark and logos are owned by the Bluetooth SIG, Inc. and any use of such marks by connectBlue is under license.