



Sample photo

Order symbol: CAB PC 604022 T
Product nbr: 8113070
Description: Cabinet, PC
Remarks: Latches on the long side

EAN: 6418074020451
El. number:
Finland: 3424176
Denmark: 8212020294
Italy: 7822065
Sweden: 2539957
Norway:

Including: Cabinet base, door with EPDM gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:		Length	Width	Height	Rating:
mm:		600	400	220	Ingress Protection (EN 60529): IP 65
inch:		23.6	15.7	8.7	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		Smoked grey			Flammability Rating (UL 746 C 5): UL 746C 5V
Gasket material:		EPDM			Glow Wire Test (IEC 695-2-1) °C: 960
Temperatures:					UL Type: UL TYPE 1, 4, 4X, 12, 13
Short term:		-40 ... 120 °C			Certificates: Germanischer Lloyd (GL) Underwriters Laboratories Fimko Lloyds Register of Shipping (LR) Europe EN 62208: 2003 UL Canada Gost R
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
EKIV 64H		Mounting plate			
EKIV 37		DIN-35 Mounting rail			
DS35370E1		DIN-35 Mounting rail			
FP A 64		Swing-out door/Front plate			
MB 12225 AL		Swing door set			
FP 64		Front plate			
FP 18x3-64		Front plate			
DRF 63/64		DIN rail frame set			

