

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

75784-0241

Status:

Active

Overview:

iPass™ Connector System

Description:

0.80mm Pitch, iPass™ I/O Surface Mount Receptacle, Vertical, Internal Assembly with Shell, 50 Circuit, 0.76µm Gold (Au), Through Hole Option, Tail Length 2.79mm, Left Key



image - Reference only

Series

Documents:

3D Model

Drawing (PDF)

Product Specification PS-75783-001 (PDF)

Application Specification AS-75783-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	I/O Connectors
Series	75784
Application	Wire-to-Board
Comments	Positive or passive latching cable available
Component Type	Receptacle
Electrical Model	Yes
Overview	iPass™ Connector System
Product Name	iPass™, PCI Express*, SAS, Serial ATA
Type	N/A
UPC	800756840109

Physical

Circuits (Loaded)	50
Circuits (maximum)	50
Color - Resin	Black
Durability (mating cycles max)	250
Flammability	94V-0
Gender	Female
Keying to Mating Part	Yes
Lock to Mating Part	None
Material - Metal	Copper-Nickel-Zinc, High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	5.000/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	2.79mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.36mm
Packaging Type	Embossed Tape on Reel
Panel Mount	No
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Ports	1

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
75784Series

Use With
iPass™ Cable Assemblies, 79575 , 79576 , 74562 , 74563 , 79536 , 74573 , 74569 , 74586

Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +80°C
Termination Interface: Style	Surface Mount, Through Hole
Waterproof / Dustproof	No
Wire Insulation Diameter	N/A
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	0.5A
Grounding to Panel	None
Voltage - Maximum	30V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-75783-001
Electrical Model Document	EE-75577-001
Product Specification	PS-75783-001
S-Parameter Model	SP-75577-001
Sales Drawing	SD-75784-001

This document was generated on 09/08/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75784-0241](#)