

CARDMASTER PC 17/16-3



Order symbol: PC 17/16-3
Product nbr: 7525165
Description: Enclosure, PC
Remarks: Smoked transparent hinged cover

EAN: 6418074056726
El. number:
Finland: 3438230
Denmark: 8212016648
Sweden: 2537302
Norway: 2536925

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

Dimensions:		Length	Width	Height	Rating:
mm:		188	160	134	Ingress Protection (EN 60529): IP 65
inch:		7.4	6.3	5.3	Impact Resistance (EN 62262): IK 08/07
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		Smoked grey			Flammability Rating (UL 746 C 5): UL 746C 5V
Gasket material:		EPDM and Polyurethane			Glow Wire Test (IEC 695-2-1) °C: 960
Temperatures:					NEMA Class: NEMA 1, 3, 3R, 4, 4X, 12, 13
Short term:		-40 ... 120 °C			Certificates:
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					Underwriters Laboratories
MP 17/16		Mounting plate			Fimko
FP 17/16		Front plate (aluminium)			Europe EN 62208: 2003
FC PC 17/16		Frame of PC front plate			UL Canada
					Gost R

CARDMASTER 166x160x108-134

