


MATERIAL: LOW DENSITY POLYETHYLENE

PART NO.	DIMENSIONS		WALL THICKNESS	WEIGHT lbs / 100 ft
	A	B		
CL T25F - 20	0.397 (10.08)	0.277 (7.04)	.0155" ±.0025"	0.75 (340.0)
CL T35F - 20	0.500 (12.7)	0.350 (8.89)	.0200" ±.0050"	1.12 (510.0)
CL T38F - 20	0.556 (14.12)	0.415 (10.54)	.0200" ±.0050"	1.38 (625.0)
CL T50F - 20	0.670 (17.02)	0.505 (12.83)	.0200" ±.0050"	1.85 (840.0)
CL T62F - 20	0.816 (20.73)	0.650 (16.51)	.0200" ±.0050"	2.29 (1040.0)
CL T75F - 20	0.935 (23.75)	0.760 (19.30)	.0200" ±.0050"	2.64 (1200.0)
CL T100F - 20	1.090 (27.69)	0.915 (23.24)	.0200" ±.0030"	3.52 (1600.0)
CL T125F - 20	1.500 (38.10)	1.290 (32.77)	.0235" ±.0065"	6.03 (2740.0)
CL T150F - 20	1.729 ±0.085 (43.92 ±2.16)	1.482 ±0.085 (39.64 ±2.16)	.0235" ±.0065"	7.39 (3360.0)
CL T188F - 20	2.169 ±0.085 (55.09 ±2.16)	1.881 ±0.085 (47.78 ±2.16)	.0235" ±.0065"	9.10 (4127.3)



1. SEE PART NUMBER SUFFIX DESIGNATION ON CURRENT PRICE SHEET FOR PACKAGE SIZE AND PART COLOR.

2. FOR ROLL SIZES LARGER THAN 10 FEET, SPLICES MAY OCCUR.

SLIT CORRUGATED TUBING										
			B: ADD WALL THICKNESS FROM POLYETHYLENE TO NYLON 6 COLUMN C: CORRECTION TO (MM) CONVERSION ON B DIM. FOR CLT13BF-20 FROM 110.39 TO 10.541							
8	6/22/11	LEF	JVL	GB0222BP	8	RAMI				
7	5/17/11	LEF	VJS	GB0222BP	7	RAMI				
			A: ADDED NOTE #2							
6	9/25/02	LG6		CHG MAT. TO LOW DENSITY POLYETHYLENE	GB0222BP	6				
5	4/5/02	LG6		CHG DIM ON A & B DIM FOR CLT150F.	GB0222BP	5				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± 0.050 (1.27) ANGLES ±										
UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.										
DRAWN BY CPE				SCALE NONE						
DATE 9-18-97				DRAWING NO.						
CHK'D VJS				DMG A						
SEE ABOVE				GB0222BP						
				SIZE						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CLT188F-C20](#) [CLT50N-4M630](#) [CLT62N-2.5M630](#) [CLT25F-C4](#) [CLT62F-C4](#) [CLT188F-C3](#) [CLT35F-C4](#) [CLT50F-C4](#)
[CLT100F-X4](#) [CLT188F-X3](#) [CLT50F-4M20](#) [CLT188F-C4](#) [CLT75N-2M630](#) [CLT38F-C3](#) [CLT35F-7M20](#) [CLT75F-](#)
[2M20](#) [CLT188N-3C630](#) [CLT150F-X3](#) [CLT75F-C4](#) [CLT62N-C630](#) [CLT188F-3C20](#) [CLT38N-5M630](#) [CLT188F-X4](#)
[CLT38F-5M20](#) [CLT188F-X20](#) [CLT62F-2.5M20](#) [CLT38F-C4](#)