





Shielded Cable Termination Semi-Rigid - Straight Solder Type End Launch



CABLE TYPE	BOARD THICKNESS	GOLD PLATED	"A"	"B"	"W"	"H"	"C"	"D"
.086 Semi-Rigid	0.062 (1.57)	142-0093-801	0.068 (1.73)	0.046 (1.42)	0.250 (6.35)	.250 (6.35)	.150 (3.81)	.032 (0.81)



1. Identify connector parts. (1 piece part)
2. Strip cable to dimensions shown. Do not nick braid or center conductor.
3. Insert cable into body making sure cable is bottomed against shoulder body. Solder body to cable. Use a minimum amount of heat to minimize cable dielectric movement.

CABLE GROUP	PART NUMBER
RG-405/u (.086 semi-rigid)	142-0093-801/806

