

首長防水ハンドル

WATERPROOF HANDLES

A-1140-H
ステンレス製A-140-H
亜鉛合金製





シャフトがのびて ちょっとした余裕ができました

特注で塗装も製作致します



A-1140-H-1-1

A-140-H-2-1


A-140-H-2-1
-IvoryキーNo.TAK60
KeyキーNo.0200
Keyパネル穴明け寸法
Panel drilling dimensions〔A-140-H-1〕
〔A-1140-H-1〕〔A-140-H-2〕
〔A-1140-H-2〕

No.TAK60

No.0200

使用例

Example of application



遮熱板の切り欠きスペースを小さくすることができ、遮熱効果がアップします。

The space of a notch of the heat shut out plate can be made small, so the effect of shutting out heat is increased.

特 徴 Feature

- 錠前は操作性に優れた防塵シャッター付新型リバーシブルキーTAK60を標準装備(A-1140-H-TAK60・A-140-TAK60)
- 従来のA-140シリーズと比較してシャフトの長さを長くしたため、操作時に遮熱板や窓枠、小窓が邪魔になりません。
- 表面仕上は耐食性に優れたマイクロポーラスクロムめっき仕上です。(A-140-H)
- 防水タイプ(Oリング・パッキン使用)
- The lock comes standard with the TAK60, a new-style reversible key with an easy-to-use dustproof shutter. (A-1140-H-TAK60, A-140-TAK60)
- The shaft is made longer than the current A-140 series so it is does not interfere with the heat shut out plate, window frame and small window when operating.
- The surface finish is microporous-chromium plating for high corrosion resistance.
- Waterproof (using O-ring and sheet packing)

仕 様

〔A-1140-H〕●材 質: ステンレス鋼铸件 (SUS316)

●表面仕上: 鏡面/バフ研磨

〔A-140-H〕●材 質: 亜鉛合金 (ZDC)

●表面仕上: クロムめっき (MZCr)

●鍵 番 号: TAK60・0200

●付 属 品: 大ナット・ビスセット・キー2本

用 途 ●屋外キュービクル・配分電盤・制御盤

納 期 ●標準在庫品(塗装は特注品です。)

備 考 ●マスターシステム、指定番番、鍵違い、鍵なしも製作します。お問合せください。

●本製品の止め金取付け用ねじは、緩み防止のため「緩み防止剤」の塗布をお奨め致します。

Specifications

〔A-1140-H〕●Material: Stainless steel cast (SUS316)

●Finish: Mirror surface buffing

〔A-140-H〕●Material: Zinc alloy (ZDC)

●Finish: Chrome plating (MZCr)

●Key No.: TAK60, 0200

●Accessories: Two keys, large nut and screws

Specific- ●Cubicles, distribution boards and use control board.

Remarks ●It is recommended that thread-locking fluid be used to prevent loosening of the mounting screws for the catch.

ハンドル・取手
つまみ・周辺機器

クレモン

ローラー
締り特装密閉
ハンドルフリーザー
密 閉平 面
スイング

ギア式

平 面
ハンドルポップ
ハンドルリフト
ハンドルアジャスト
ハンドル

ラッチ式

スナッチ

リンク

フック式

ロック
ハンドル

L-SHAPED HANDLES

L 型
ハンドルT 型
ハンドル丸型
小型

押ボタン

取 手

つまみ

止め金
ロッド棒ジョイント
リンク

ワイヤ

18.01

TAKIGEN
総合 24

503

商品番号 Product No.	RoHS	CAD	L	W1	W2	□W3	(W4)	(H1)	H2	H3	H4	H5	(H6)	P	φD	φd	最大適用板厚 Max. applicable panel thickness	製品質量(g) Mass	コード Code	単 価 Price	量販価格 Bulk Price
A-1140-H-1-1-TAK60	●	2D	152	30	16	10	35	70	6	22	22.5	8	46.5	40	60	8	8.5	609	04138	¥10,500	5個～ ¥10,100
A-1140-H-1-1	●	2D	152	30	16	10	35	70	6	22	22.5	8	46.5	40	60	8	8.5	609	03372	¥10,500	5個～ ¥10,100
A-1140-H-2-1-TAK60	●	2D	120	24	14	8	30	56	5	12	14.3	5	37.5	32	48	7	5.5	333	04139	¥9,500	5個～ ¥9,120
A-1140-H-2-1	●	2D	120	24	14	8	30	56	5	12	14.3	5	37.5	32	48	7	5.5	333	03374	¥9,500	5個～ ¥9,120
A-140-H-1-1-TAK60	●	2D	152	30	16	10	35	70	6	22	22.5	8	46.5	40	60	8	8.5	517	04037	¥1,900	15個～ ¥1,824
A-140-H-1-1	●	2D	152	30	16	10	35	70	6	22	22.5	8	46.5	40	60	8	8.5	517	03295	¥1,900	15個～ ¥1,824
A-140-H-2-1-TAK60	●	2D/3D	120	24	14	8	30	56	5	12	14.3	5	37.5	32	48	7	5.5	286	04038	¥1,650	20個～ ¥1,584
A-140-H-2-1	●	2D/3D	120	24	14	8	30	56	5	12	14.3	5	37.5	32	48	7	5.5	286	03299	¥1,650	20個～ ¥1,584

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。