

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130099-0129](#)
Status: **Active**
Overview: [Strain-Relief Cord Grips](#)
Description: MAX-LOC® Strain Relief Cord-Sealing Grip, 1" NPT, 90° Angle Male, Cable Diameter 19.05-22.23mm (.750-.875"), Stainless Steel Mesh



Series

image - Reference only

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR32159

General

Product Family Cable Grips
Series [130099](#)
Eye Type N/A
NEMA Rating NEMA 3R
O-Ring No
Overview [Strain-Relief Cord Grips](#)
Product Literature Order No 987650-8064
Product Name MAX-LOC®
Type Strain Relief Grip
UPC 78678855574
Use With MAX-LOC® Lock Nut 1" NPT [130099-0145](#) , MAX-LOC® Gasket Sealing Ring 1" NPT [130099-0151](#) , MAX-LOC® O-Ring, 1" NPT [130180-0334](#)

Woodhead Yes

Physical

Approximate Break Strength N/A
Bale Length N/A
Body Style 90° Angle
Cable Diameter 19.05-22.23mm (.750-.875")
Color - Grommet N/A
Gender Male
Material - Body Nylon
Material - Grip Stainless Steel
Mesh Length N/A
Net Weight 8.610/kg
Number of Holes 1
Thread Size 1" NPT

Material Info

Old Part Number 5557M

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130099Series](#)