

Polyester Labels (B-423, B-430, B-432, B483, B-489)


For general purpose industrial ID applications.

- Widely used for PC board component ID, bin and shelf labels, barcoding and asset tracking
- 3 levels of adhesive strength

B-423, B-483, B-489: Service temp: -94°F to 248°F

B-430, B432: Service temp: -40°F to 212°F

All materials have approvals:



Fits Printer Model(s)	Diagram	Catalog #	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Horiz. Repeat C Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon
Standard adhesive (B-423 white, B-430 clear):											
BBP33 only	Fig. 1	B33-5-423	Gloss White	1.000 (25.4)	0.500 (12.7)	1.075 (27.3)	0.600 (15.2)	3.350 (85.1)	3	5000	B30-R6000
BBP33 only	Fig. 2	B33-17-423	Gloss White	2.000 (50.8)	1.000 (25.4)		1.125 (28.6)	2.200 (55.9)	1	1500	B30-R6000
BBP33 only	Fig. 2	B33-17-430	Clear	2.000 (50.8)	1.000 (25.4)		1.125 (28.6)	2.200 (55.9)	1	1500	B30-R6000
BBP33 only	Fig. 2	B33-18-423	Gloss White	3.000 (76.2)	1.000 (25.4)		1.125 (28.6)	3.200 (81.3)	1	1500	B30-R6000
BBP33 only	Fig. 2	B33-18-430	Clear	3.000 (76.2)	1.000 (25.4)		1.125 (28.6)	3.200 (81.3)	1	1500	B30-R6000
Stronger adhesive for textured surfaces (B-432 clear):											
BBP33 only	Fig. 1	B33-5-432	Clear	1.000 (25.4)	0.500 (12.7)	1.075 (27.3)	0.600 (15.2)	3.350 (85.1)	3	5000	B30-R6000
BBP33 only	Fig. 2	B33-17-432	Clear	2.000 (50.8)	1.000 (25.4)		1.125 (28.6)	2.200 (55.9)	1	1500	B30-R6000
BBP33 only	Fig. 2	B33-18-432	Clear	3.000 (76.2)	1.000 (25.4)		1.125 (28.6)	3.200 (81.3)	1	1500	B30-R6000
BBP33 only	Fig. 2	B33-19-432	Clear	3.000 (76.2)	2.000 (50.8)		2.125 (54.0)	3.200 (81.3)	1	500	B30-R6000
Ultra aggressive adhesive for highly textured surfaces (B-483 and B-489 white):											
BBP33 only	Fig. 1	B33-5-483	Gloss White	1.000 (25.4)	0.500 (12.7)	1.075 (27.3)	0.600 (15.2)	3.350 (85.1)	3	5000	B30-R6000
BBP33 only	Fig. 1	B33-5-489	Matte White	1.000 (25.4)	0.500 (12.7)	1.075 (27.3)	0.600 (15.2)	3.350 (85.1)	3	5000	B30-R4300
BBP33 only	Fig. 2	B33-17-483	Gloss White	2.000 (50.8)	1.000 (25.4)		1.125 (28.6)	2.200 (55.9)	1	1500	B30-R6000
BBP33 only	Fig. 2	B33-17-489	Matte White	2.000 (50.8)	1.000 (25.4)		1.125 (28.6)	2.200 (55.9)	1	1500	B30-R4300
BBP33 only	Fig. 2	B33-18-483	Gloss White	3.000 (76.2)	1.000 (25.4)		1.125 (28.6)	3.200 (81.3)	1	1500	B30-R6000
BBP33 only	Fig. 2	B33-19-483	Gloss White	3.000 (76.2)	2.000 (50.8)		2.125 (54.0)	3.200 (81.3)	1	500	B30-R6000
BBP33 only	Fig. 2	B33-18-489	Matte White	3.000 (76.2)	1.000 (25.4)		1.125 (28.6)	3.200 (81.3)	1	1500	B30-R4300
BBP33 only	Fig. 2	B33-19-489	Matte White	3.000 (76.2)	2.000 (50.8)		2.125 (54.0)	3.200 (81.3)	1	500	B30-R4300

Metallized Polyester Labels (B-428, B-434, B-486, B-438)

For product labeling, asset tracking and general industrial ID.

- Silver metallic label withstands solvents and variable temperatures
- Ideal for serial number plates and rating plates with name-plate quality and metal-looking finish
- 3 adhesive strengths/gloss configurations to meet your needs



B-428: Service temp: -40°F to 293°F

B-434: Service temp: -40°F to 194°F

B-486: Service temp: -40°F to 248°F

B-438: Service temp: -40°F to 104°F

All: Agency approvals:



Fits Printer Model(s)	Diagram	Catalog #	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Horiz. Repeat C Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon
Standard adhesive for smooth surfaces (B-428):											
BBP33 only	Fig. 1	B33-5-428	Matte Silver	1.000 (25.4)	0.500 (12.7)	1.075 (27.3)	0.600 (15.2)	3.350 (85.1)	3	5000	B30-R4300
BBP33 only	Fig. 2	B33-17-428	Matte Silver	2.000 (50.8)	1.000 (25.4)		1.125 (28.6)	2.200 (55.9)	1	1500	B30-R4300
BBP33 only	Fig. 2	B33-18-428	Matte Silver	3.000 (76.2)	1.000 (25.4)		1.125 (28.6)	3.200 (81.3)	1	1500	B30-R4300
Stronger adhesive for rougher surfaces (B-434):											
BBP33 only	Fig. 1	B33-5-434	Gloss Silver	1.000 (25.4)	0.500 (12.7)	1.075 (27.3)	0.600 (15.2)	3.350 (85.1)	3	5000	B30-R6000
BBP33 only	Fig. 2	B33-17-434	Gloss Silver	2.000 (50.8)	1.000 (25.4)		1.125 (28.6)	2.200 (55.9)	1	1500	B30-R6000
BBP33 only	Fig. 2	B33-18-434	Gloss Silver	3.000 (76.2)	1.000 (25.4)		1.125 (28.6)	3.200 (81.3)	1	1500	B30-R6000
BBP33 only	Fig. 2	B33-19-434	Gloss Silver	3.000 (76.2)	2.000 (50.8)		2.125 (54.0)	3.200 (81.3)	1	500	B30-R6000
Ultra aggressive adhesive for highly textured, powder coated and low surface energy surfaces (B-486):											
BBP33 only	Fig. 1	B33-5-486	Matte Silver	1.000 (25.4)	0.500 (12.7)	1.075 (27.3)	0.600 (15.2)	3.350 (85.1)	3	5000	B30-R4300
BBP33 only	Fig. 2	B33-17-486	Matte Silver	2.000 (50.8)	1.000 (25.4)		1.125 (28.6)	2.200 (55.9)	1	1500	B30-R4300
BBP33 only	Fig. 2	B33-18-486	Matte Silver	3.000 (76.2)	1.000 (25.4)		1.125 (28.6)	3.200 (81.3)	1	1500	B30-R4300
BBP33 only	Fig. 2	B33-19-486	Matte Silver	3.000 (76.2)	2.000 (50.8)		2.125 (54.0)	3.200 (81.3)	1	500	B30-R4300
Tamper-Evident - Leaves checkerboard footprint on surface and on label if removed to prevent re-use (B-438):											
BBP31, BBP33	Fig. 2	B30-17-438	Matte Silver	2.000 (50.8)	1.000 (25.4)		2.500 (63.5)	1.125 (28.6)	1	1225	B30-R4300
BBP31, BBP33	Fig. 2	B30-18-438	Matte Silver	3.000 (76.2)	1.000 (25.4)		3.250 (82.6)	1.250 (31.8)	1	1225	B30-R4300
BBP31, BBP33	Fig. 2	B30-222-438	Matte Silver	3.000 (76.2)	2.000 (50.8)		3.250 (82.6)	2.250 (57.2)	1	650	B30-R4300
BBP31, BBP33	Fig. 3	B30C-3000-438-SL	Matte Silver	3.000 (76.2)	100 ft. (30.5m)			3.250 (82.6)	- continuous supply -		B30-R4300