

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301080197](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Super-Safeway Wet Location 100W Fluorescent Tube Light with 4 Lamps, Cord Type 16/3 SOOW, Cord Length 1.22m (4.0')

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	LR85374
UL	E174254

General

Product Family	Portable Lighting
Series	130108
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Outlet	Feed-Through
Overview	Wide-Area Lighting Products
Product Name	Super-Safeway
Type	Wide Area Lamps
UPC	78678867194

Physical

Cord Length - Primary	1.22m (4.0')
Cord Length - Secondary	0.152m (6.00")
Depth	101.60mm (4.000")
Duty	Industrial
Guard Included	Yes
Guard Type	Clear Butyrate
Height	N/A
Length	1.43m (56.250")
Material - Guard	Butyrate
Mounting Style	Straps
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Fluorescent
Cord Type - Primary	16/3 SOOW
Lamp Type	F25/T8
Lamp Wattage - Maximum	100W
Lumens	8320
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info

Engineering Number	2012
--------------------	------



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130108](#) Series