


KEYBOARD : 105KEYS

DIMENSIONS :
44.2mm(H), 426mm(W), 435mm(D)

Europe

Master Enterprise
www.master.co.uk sales@master.co.uk
TEL:+44 870 770 4594
FAX:+44 870 770 4595

Asia/USA

CDS Enterprise
www.urack-cds.com.tw sales@urack-cds.com.tw
TEL:886-2-29924116
FAX:886-2-29924146

► **LCD DISPLAY : 15" TFT ACTIVE MATRIX PANEL**

DISPLAY SIZE : 304.1 X 288.1 mm

PITCH : 0.297x0.297 mm

MAX RESOLUTION : 1024 X 768

CONTRAST RATIO : 300:1

BRIGHTNESS : 250

RESPONSE TIME :
30mS(RISING), 10mS(FALLING)

DISPLAY COLOR : 16M(DITHERING)

VIEWING ANGLE :
+18°~-18° (L/R), +80°~-80° (U/D)

INPUT SIGNAL
VIDEO : VIDEO R.G.B ANALOG 0.7V P. TOP.
SYNC : SYNC TTL POSITIVE OR NEGATIVE

DISPLAY PARADIGM : VGA/SVGA/XGA

OPERATION TEMPERATURE/HUMIDITY:
-20°C~60°C / 20%~80%

SIGNAL CONNECTOR : 15 PIN MINI D-SUB

FRONT CONTROL :
POWER SWITCH, MENU, SELECT(UP/DOWN), AUTO

OSD :
AUTO-ADJUSTMENT, CONTRAST, BRIGHTNESS
CLOCK, PHASE, HV-POSITION, LOAD DEFAULT
COLOR TEMPERATURE

INPUT SELECT : VGA.