

DDM/CAD

21 FEB 83

16 JUL 83

15 MAR 91

DCS

GLH

GLH

GLH

REVISIONS

A	PR12536	16 JUL 83
B	CO55506	16 JUL 83
C	CO55828	16 JUL 83
D	CO56632	16 JUL 83
E	CO69973	16 JUL 83

ISSUE

6



DRAWING NUMBER

M

38HM4

RELEASE NO PR-12536-T

REPLACES



- NOTES
- 1 - UNIT INCLUDES 8HM103 BASIC SWITCH
 - 2 - SWITCH HERMETICALLY SEALED PER MIL-S-8805, SYMBOL 5
 - 3 - ALL EXPOSED PARTS ARE CORROSION RESISTANT MATERIALS OR SURFACE TREATED
 - 4 - LEADWIRE PER MIL-W-22759/10-20 AND 36 INCHES LONG REF

ELECTRICAL DATA	
CONTACT ARRANGEMENT S P N C	
28 VOLTS DC RATING	
INDUCTIVE	SEA LEVEL - 1/4 AMP
	70,000 FT - 1/4 AMP
RESISTIVE	SEA LEVEL - 1 AMP
	70,000 FT - 1 AMP

CHARACTERISTICS	
OPERATING FORCE	5 LBS MAX
RELEASE FORCE	12 OZ MIN
PRETRAVEL	.006 MIN
DIFFERENTIAL TRAVEL	.015 MAX
OVERTRAVEL	.025 MIN

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

MICRO SWITCH

a Honeywell Division

SWITCH-BASIC

5903922

CATALOG LISTING

38HM4

SUNSTRAND DRAWING

5903922

THIRD ANGLE PROJECTION			
SCALE 2:1			
DO NOT SCALE PRINT			
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE			
ONE PLACE	()	±	.030
TWO PLACES	(00)	±	.015
THREE PLACES	(000)	±	.005
ANGLES		±	
WEIGHT			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[38HM4](#)