





Dimensions: mm (IN)

**Mechanical Specifications:**

- Mechanical life: 10,000 operation min. per switch
- Operation force: less than 800g

Electrical Specifications:

- Electrical life: 5,000 operation min. per switch
- Rating: Non-switching 100mA/50VDC;
Switching 50mA/24VDC

Soldering Process:

- Wave soldering: recommended solder temperature at 500°F (260°C) max. 5 seconds
- Hand soldering: use a soldering iron of 30 watts or less, controlled at 608°F (320°C) approximately 2 seconds while applying solder

Mouser Stock No.	No. of Positions	Dimension "A" (In.)	Type
106-1254	4	.439	SPST
106-1258	8	.839	SPST

Right Angle DIP Switches
106-1254, 106-1258

**Mountain
Switch**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[106-1258](#) [106-1254](#)