


JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
SM0620M	6.0	.020	.024	0.30	5,000	C-6
SM0650M	6.0	.050	.080	1.01	5,000	C-2R
SM1220M	12.0	.020	.032	0.40	5,000	C-2V
SM1240M	12.0	.040	.088	1.11	5,000	C-2V
SM1250M	12.0	.050	.159	2.00	5,000	C-2V
SM2420M	24.0	.020	.064	0.80	5,000	C-2F
SM2430M	24.0	.030	.159	2.00	5,000	C-2F
SM2450M	24.0	.050	.279	3.51	5,000	C-2F
SM3020M	30.0	.040	.287	3.61	5,000	C-2F
SM3040M	30.0	.040	.287	3.61	5,000	C-2F

METRIC



THIRD ANGLE
PROJECTION

DIMENSIONS ARE
IN MILLIMETERS

TOLERANCE UNLESS
OTHERWISE SPECIFIED

1 PL +/- 0.2
2 PL +/- 0
ANGLE +/- 0

DRAWN BY
L. WENGSTROM

APPV'D BY DATE
QC 8/16/00

JKL

COMPONENTS CORPORATION

TITLE
T-1 1/4 TELEPHONE SLIDE BASE
LILIPUT T4.6

SIZE
A

FSCM NO.
55335

DRAWING
NO.

SLIDE BASE LILIPUT T4.6

REV. NO. DESCRIPTION/ECO NUMBER

- CAD DRAWING -
MANUAL REVISIONS NOT PERMITTED

SCALE
NONE

RELEASED
DATE 8/16/00

REVISION
DATE

REV.
NO.

SHEET
1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[SM1240M](#) [SM2420M](#) [SM2450M](#)