

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0190360003
Status: Active
Description: Avikrimp™ Snap Plug, for 18-22 AWG Wire, Box, 22.78mm (.897") Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)


General
Product Family Quick Disconnects
Series 19036
Comments Extruded Nylon Insulation
Product Name Avikrimp™
Type Snap Plug

Physical
Barrel Type Closed
Flammability 94V-2
Gender Male
Glow-Wire Compliant No
Insulation Nylon (PA)
Lock to Mating Part None
Material - Metal Copper
Orientation Straight
Packaging Type Bag
Tab Thickness N/A
Tab Width N/A
Wire Insulation Diameter 3.60mm (.142") max.
Wire Size AWG 18, 20, 22
Wire Size mm² 0.35 - 0.80

Electrical
CSA LR18689
UL E152602
Voltage - Maximum N/A

Material Info
Old Part Number A-869

Reference - Drawing Numbers
Sales Drawing SD-19036-001



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19036Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	0640010100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION