

YAE22G13BOX


BURNDY® PRODUCTS

YAE22G13BOX

YAE22G13BOX : 26-20 NYLON RING 4-6
STU



ACTIVE



[Assistant](#)

[Add to Favorites](#)

 [Email Datasheet](#)  [Print Datasheet](#)

FCI Brings You More

 [Contact our sales/technical support](#)

 [Sample request](#)

 [Price request](#)

Specifications

[Download document](#)

Dimensional Physical Approvals / Certifications Other Features

Dimensional

Stud Hole (Size)	#6 #4
Tongue Width (in)	0.25 in.
Wire Insulation Grip	Yes
Insulation Diameter (Max)	0.098 in.

Physical

Conductor Size	24 AWG 20 AWG 22 AWG 26 AWG
Element A Index	Hand Tools
Insulation Type	Nylon
Color Code	Amber
Conductor Size (Range)	26 AWG to 20 AWG

Approvals / Certifications

Military Listed	Yes
UL Listed	No
CSA Certified	Yes

Other Features

Tape Mounted Catalog Number	YAE22G13M
Tongue Type	Ring
Bulk Catalog Number	YAE22G13
UPC	78181002326
Keyword	smterm