


UNIT:mm

4

3

2


1



CONN OUTER MOLD: WM-020

CONN OUTER MOLD: WM-020

PN




PIN ASSIGNMENT

P1		P2
1	RED	1
2	WHITE	2
3	SPIRAL	3

Electronic Test:

- 1.100% Test,(Open,Short,Miss Wire)
- 2.Contact Resistance:2 ohm max.
- 3.Insulation Resistance:10M ohm min.
- 4.Hi-Pot:100V DC/10ms



⑦	TIE	1	BLACK L=50mm
⑥	TUBE	2	HEAT SHRINK TUBE BLACK OD1.5*L15mm.
⑤	PE BAG	1/10	CLEAR SIZE:280*330*0.05mm PRINT BLACK"MADE IN CHINA"+ "10PCS"
④	PE BAG	1	CLEAR SIZE:130*230*0.05mm PRINT BLACK"MADE IN CHINA".
③	OUT JACKET	5.5g	OUTER MODEL PVC 45P COLOR BLACK
②	CONN	2	3.5ST MALE Tray6.0mm L=30mm MOLD TYPE NI-PLATED INSULATOR COLOR:BLACK
①	CABLE	1	NOUL 28AWG(7/0.12 TC)*2C(RED,WHITE)+S(43/0.12 TC) JACKET BLACK OD:3.0MM
NO.	NAME	Q'TY	SPECIFICATION

CNC Tech, LLC

Industrial Cable and Connector Technology

DRAWED BY LICHENG DARWING ND.

CHECKED BY		CUSTOMER	
------------	--	----------	--

APPROVAL BY	ITEM NO.	770-10040-00050
-------------	----------	-----------------

DECIDE BY		DATE	2012-12-17
-----------	--	------	------------

VERSIONS/EDITION	A/0	PROJECTION	
------------------	-----	------------	---

4

3

2

1