

MIDGET, SPF (5AG) FUSE HOLDER

- Designed for SPF (Solar Protection Fuse) • Optional cover will protect and insulate fuse • Flame resistant

SPECIFICATIONS

Base & Cover: Nylon, UL Rated 94V-0


Clips: .030 (.76) Brass, Matte Tin Plate

Rated: 30 Amps


Operating Temp. Range: -58°F to +292°F (-50°C to +145°C)



3576 (THM)



Optional Cover Cat. No. 3576C fits Cat. No. 3576 & 3574




3574 (SMT)

CAT. NO. 3576 - Holder

CAT. NO. 3576C - Cover only


Mounting Detail



CAT. NO. 3574 - Holder

CAT. NO. 3576C - Cover only

Mounting Detail



3AG FUSE BLOCKS

- Available with fiberglass or phenolic base
- Fuse clips riveted to base for rugged applications

SPECIFICATIONS

Phenolic Base: XP, Black UL Rated 94-HB


Fiberglass Base: GPO-3 UL Rated 94 V-0

Clips: .020 (.51) Brass - Nickel Plated

Rated: 15 Amps @ 500 VAC


Operating Temp. Range: -58°F to +292°F (-50°C to +145°C)

BLACK PHENOLIC	FIBER-GLASS	HOLDS NO. OF FUSES	W
CAT. NO.	CAT. NO.		
3536	3540	1	.500 (12.7)
3537	3541	2	1.125 (28.6)
3538	3542	3	1.750 (44.5)
3539	3543	4	2.375 (60.3)




FUSE COVERS

- Made from flame retardant material
- Protects fuse from shorting and minor bumps



MATERIAL: PVC, UL Listed 94V-0

CAT. NO.	FUSE SIZE	L	W	H
3527C	5mm x 20mm	.945 (24.0)	.314 (8.0)	.512 (13.0)
3521C	2AG	.787 (20.0)	.295 (7.5)	.452 (11.5)
4245C	3AG	1.319 (33.5)	.472 (12.0)	.591 (15.0)




Can be used with clips or fuse holders



Can be used with clips 3512, 3512P, 3517 and 3518

MATERIAL: ABS, UL Rated 94V-0

CAT. NO.	FUSE SIZE
3517C	5mm x 20mm



SUBMINIATURE FUSE HOLDERS

- Reliable spring tension assures low contact resistance
- Fuse holders allow for quick changing of subminiature fuses
- Ideal for high density circuit board applications

SPECIFICATIONS

Base: Thermoplastic, UL Rated 94V-0

Springs: Beryllium Copper, Gold Plate

Pins: Brass, Tin Plate

Current Rating: 5 Amps @ 250V AC




.335 (8.5) x .158 (4.0) FUSE

For Littelfuse 392/395 Type TE5®
Bussmann: PC Series
or equivalent




.335 (8.5) DIA. FUSE


For Littelfuse 370 Type TR5®
Bussmann: BK-EFF series
or equivalent




CAT. NO. 3552



CAT. NO. 3553



CAT. NO. 3556



CAT. NO. 3554