

Coaxial Cable Connector 11_BNC-50-2-1/133_N

Description

Straight cable plug

Interface standards

IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 4 GHz

Mechanical Data

Centre contact soldered
Outer 2contact clamped
Weight 0.0173 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing DOU-00007910
Catalogue drawing DOU-00007659
Assembly instruction DOC-0000179064

Ordering Information

Single package 11_BNC-50-2-1/133_NE
Bulk 100 pcs package 11_BNC-50-2-1/133_NH

Additional Information

Suitable cables RG_316_U, ENVIROFLEX_316, RG_188_A/U, RG 174 /U