







PARALLEL SPLICES

Material: Copper												
	Krimptite®				Insulkrimp® (PVC Insulation)		Versakrimp™				Nylakrimp® (Nylon Insulation)	
Wire Range AWG	Order No.	ID Minimum	OD Maximum	Max. Length L	Order No.	Max. Length L	Order No.	ID Minimum	OD Maximum	Max. Length L	Order No.	Max. Length L
18-22 (0.80-0.35)					19206-0002*	18.10 (.712)	19207-0001*	1.50 (.060)	3.30 (.130)	8.40 (.332)	19207-0002*	17.00 (.670)
14-16 (2.00-1.30)	19208-0001	2.10 (.084)	4.20 (.165)	8.60 (.340)	19206-0004	18.70 (.735)	19205-0001*	2.30 (.091)	4.10 (.160)	8.40 (.330)	19207-0004*	16.40 (.645)
					19206-0005*	18.70 (.735)						
10-12 (5.00-3.30)	19208-0002	3.30 (.128)	5.80 (.230)	8.40 (.330)	19206-0008	12.10 (.831)	19205-0003*	3.30 (.130)	5.70 (.225)	8.40 (.330)	19207-0005*	17.50 (.688)
					19206-0010*	12.10 (.831)						
8 (8.50)							19205-0004	4.20 (.165)	7.50 (.295)	10.40 (.408)		
6							19205-0006	5.80 (.230)	9.50 (.374)	12.10 (.477)		
4							19205-0007	7.00 (.277)	11.60 (.457)	13.90 (.547)		
2							19205-0008	9.00 (.357)	13.70 (.538)	17.20 (.680)		
1/0							19205-0009	11.20 (.439)	15.70 (.620)	20.10 (.790)		
2/0							19205-0010	12.60 (.496)	17.70 (.697)	19.80 (.779)		
3/0							19215-0049	13.80 (.545)	19.30 (.760)	20.30 (.800)		
4/0							19215-0050	15.80 (.621)	21.80 (.860)	20.80 (.820)		

Product Specifications			
Wire Range AWG	Insulation Color	Maximum Wire Insulation Diameter	
		Insulkrimp	Nylakrimp®
18-22 (0.80-0.35)	Red	3.70 (.145)	3.00 (.120)
14-16 (2.00-1.30)	Blue	4.40 (.175)	3.80 (.150)
10-12 (5.00-3.30)	Yellow	6.60 (.260)	5.30 (.210)

3 AND 4 WAY CONNECTORS

Material: Copper				
	Insulkrimp (PVC Insulation)	Insulkrimp (PVC Insulation)	Avikrimp (Nylon Insulation)	Avikrimp (Nylon Insulation)
Wire Range AWG	Order No.			
18-22 (0.80-0.35)	19204-0004	19204-0003	19204-0009	19204-0008
14-16 (2.00-1.30)	19204-0014	19204-0013	19204-0018	19204-0017
10-12 (5.00-3.30)	19204-0026	19204-0025	19204-0030	19204-0029

* Part has seamless barrel instead of butted seam