

SMC Goes To Great Lengths

- ✓ Standard stocked lengths at 66ft, 100ft, 500ft, 1000ft, and 1640ft.
- ✓ Other lengths available based on minimum order quantity

SMC Tubing Accessories

- ✓ TK-1 Tube Cutter (Tubing 13mm or less)
- ✓ TK-2 Tube Cutter (Tubing 18mm or less)
- ✓ TK-3 Tube Cutter (Low Cost)
- ✓ TG-1 Tube Release Tool (ø4, ø6mm tube)
- ✓ TG-2 Tube Release Tool (ø1/8", ø1/4" tube)



SMC Offers a Rainbow of "Standard" color choices

Polyurethane Tubing		TIUB 05 BU 33		Length per roll	
Size		Color indication		Symbol	Roll size
Symbol	Tube size	Symbol	Color	20	66 ft.
01	1/8"	See Color Chart Below.		33	100 ft.
05	3/16"			153	500 ft.
07	1/4"			305	1000 ft.
11	3/8"			500 [†]	1640 ft.
13	1/2"				

[†] 1/8", 3/16", 1/4"
Longer lengths available upon request.

Polyurethane Tubing		TU 0425 BU 20		Length per roll	
Size		Color indication		Symbol	Roll size
Symbol	Tube size	Symbol	Color	20	20m
0425	4mm (5/32")	See Color Chart Below.		33*	100 ft.
0604	6mm			100	100m
0805	8mm (5/16")			153*	500 ft.
1065	10mm			305*	1000 ft.
1208	12mm			500 [†]	500m

[†] 4mm, 6mm, 8mm
* Standard for 4mm (5/32") & 8mm (5/16") tube size.
Longer lengths available upon request.

	Color	Tube Sample		Color	Tube Sample
B	Black		G4	Dark Green	
BU	Blue		GR1	Gray (solid)	
C	Clear		GR2	Lt. Gray (solid)	
G	Green		P1	Neon Pink	
R	Red		PU1	Purple (solid)	
W	White		PU2	TR Purple	
Y	Yellow		R1	Red (solid)	
YR	Orange		R2	TR Red	
BU1	Blue (solid)		S1	Silver	
BU2	TR Blue		Y1	Yellow (solid)	
BU3	Med. Blue		Y2	TR Yellow	
BR1	Brown (solid)		Y3	Neon Yellow	
G1	Green (solid)		YR1	TR Orange	
G2	TR Green		YR2	Neon Orange	
G3	Neon Green				

Note: Quick ship colors include: Black, Blue, Clear, Green, Red, White, Yellow and Orange.