



## Sockets

### KUN 30



Product	KUN 30
description	Shatter-proof, flexible, insulated coupling for a 4 mm diameter plug and solder connection up to a cable cross-section of 2.5 mm <sup>2</sup> . Nickel-plated brass socket.
operating instruction	BA405
article-no. / *colour	9318041xx  00 black    01 red    02 blue    03 yellow    04 green    07 white <div style="text-align: right; border: 1px solid black; padding: 2px;"><b>Ni</b></div>
drawing	
technical data	
connection	solder connection
rated voltage <sup>(1)</sup>	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O <sup>(3)</sup>
rated current <sup>(1)</sup> (consider derating curve)	16 A
material socket	brass, nickel plated
housing material	PVC-P
temperature range acc. To IEC61010 <sup>(2)</sup>	-25 °C to +70 °C
standard	IEC 61010

4 mm system

<sup>(1)</sup> for normal environmental conditions -5°C to +40°C

<sup>(2)</sup> contact the manufacturer for applications at deviating temperature ranges

<sup>(3)</sup> without rated measurement category, for other circuits that are not directly connected to mains

stand: 17.09.2018