

4		3		2		1		
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION				
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION.				ALL INTERNATIONAL RIGHTS RESERVED.				
LOC G		DIST 14		REVISIONS				
P		LTR		DESCRIPTION		DATE	DWN	APVD
		H1		REVISED PER ECO-11-002228		11FEB11	HMR	DR

.437 MAX WASHER R.

DIMPLED SURFACE

BODY

SLEEVE

"E" MAX

"L" MAX

.431

.265±.005 DIA (FOR 1/4 STUD)

1

2

3

4

5

6

STAMP AMP 8* LOCATE APPROX AS SHOWN

TONGUE MATERIAL THK .040±.003

TAPE ITEMS ARE ON 1.200 CENTERS

COPPER PER ASTM B-152, PVC, COLOR-RED

TIN PLATE PER ASTM B-545

PRELIMINARY – NOT FOR PREPRODUCTION

.330		1.394	1.587	500	55621-7 ON TAPE	6	55621-8
				100	LOOSE PIECE	6	55621-7
.360		1.354	1.561	500	55621-1 ON TAPE	55621-2	
				100	LOOSE PIECE	55621-1	
WIRE INSULATION OD MAX		"E"	"L"	QTY	PACKAGE TYPE	PART NO	

MAX RECOMMENDED OPERATING TEMPERATURE: 105°C	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.S. GOULDEN 10-12-93		Tyco Electronics Corporation Harrisburg, PA 17105-3608		
			CHK R. HERSEY 10-12-93				
VOLTAGE RATING: 600 V MAX	DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M ELLIS 10-12-93		NAME	
CIRCULAR MIL AREA: 6.64-10.54mm² [13,100-20,800] STRANDED		0 PLC ± -		PRODUCT SPEC		TERMINAL, RING TONGUE, PLASTI-GRIP, WIRE SIZE: 8 AWG	
		1 PLC ± -		NOT AVAILABLE			
		2 PLC ± 0.20[.008]		APPLICATION SPEC			
		3 PLC ± -		114-2161		SIZE	
		4 PLC ± -		WEIGHT -		CAGE CODE	
		ANGLES ± -		CUSTOMER DRAWING		DRAWING NO	
		FINISH				RESTRICTED TO	
	4	5					

A300779		C-55621		SCALE 4:1		SHEET 1 OF 1		REV H1	
---------	--	---------	--	-----------	--	--------------	--	--------	--